


Male Disconnect - Insulated
Part No: FVDDM2216T250

SYM.	CHANGES	BY	DATE



Max Electric Current: 22-16 AWG : 10 Amp
Max Electric Rating: 75° C / 600 V Max
Tolerance ±.05
Measurement units: inches (mm)



HOFFMAN PRODUCTS

20700 Hubbell Avenue, Oak Park, MI 48237
Tel: 1-800-645-2014 • Fax: 1-800-908-1295
Web: www.hoffmanproducts.com

DATE:

TITLE:

Male Disconnect

SCALE:

FREE

PART NO.

FVDDM2216T250

DRAWING NO.

H1531

PART NAME

ISSUE

HOFFMAN CADFILE

NO.	1	2	3
NAME	CONNECTOR	VINYL	TAB
MAT'L.	BRASS	INSULATION	.250 X .032
REMARKS	TIN PLATED	RED	
APPROVED BY:	CHECKED BY:	DRAWN BY:	