




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS				DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
			VFE	19-10-10	JAG	19-10-10	XXX	02-11-10	



Notes:

Material : C1008 Steel
Plating : Bright nickel chrome
Ring Diameter : 1.8mm
Rib Diameter : 2.3mm

Part Number Table

Description	Part Number
Wire Fan Guard	MC33024

Dimensions : Inches (mm)

TOLERANCES:

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE: Wire Fan Guard			
VEE	19-10-10	SIZE	DWG. NO.	ELECTRONIC FILE	
CHECKED BY:	DATE:	A	MC33024	87P0757	REV
JAG	19-10-10				A
APPROVED BY:	DATE:	SCALE:	U.O.M.: Millimeters	SHEET:	1 OF 1
XXX	02-11-10	NTS			