





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			JAG	19-10-10	M/RD	19-10-10	XXX	02-11-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No.: 1398



Note:
 Fans: 3 X 105 cfm, ball bearing
 230 v, 50/60 Hz, 0.1 Amp
 UL/CE
 Power Cord: 6 feet, 18/3 SJT with
 Strain Relief
 Nema 6-15P
 Fan Guards: Steel C1010
 Nickel Chrome Plated
 UL Spacing
 Pre-Wired: SPT-1 18/2 Expandable with
 Part # MC33042, 6 or 9
 Fans

Part Number Table

Description	Part Number
Fan Tray Assembly	MC33039

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

JAG

DATE:

19-10-10

DRAWING TITLE:

Fan Tray Assembly

CHECKED BY:

MRD

DATE:

19-10-10

SIZE DWG. NO.

A MC33039

ELECTRONIC FILE

87P0761

APPROVED BY:

XXX

DATE:

02-11-10

SCALE: NTS

U.O.M.: Millimeters

SHEET:

1 OF 1

REV

A