





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	25-10-10	JAG	xxx	xxx	02-11-10

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398



Dimensions : Inches (mm)

NOTE

Fans: 3 X 105 cfm, ball bearing  
 230V, 50/60Hz  
 3 X 42 dBA  
 UL/CE  
 Fan Guards: Steel C1010  
 Nickel Chrome Plated  
 UL spacing  
 Pre-wired: SPT-1 18/2

Part Number Table

Description	Part Number
Fan Tray Module	MC33042

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

DRAWN BY:

DATE:

DRAWING TITLE:

Fan Tray Module

CHECKED BY:

DATE:

SIZE DWG. NO.

MC33042

ELECTRONIC FILE

87P0764

APPROVED BY:

DATE:

xxx

02-11-10

SCALE: NTS

U.O.M.: Millimeters

SHEET:

1

OF 1

REV

A