



English
日本語

Product Catalog Engineering Info Company Links Contact Us

**Fan Motors
Engineering
Information**

- DC Fans**
 - 1.Common Spec.
 - 2.Numbering (Axial Fans)
 - 3.Numbering (FB)
 - 4.Numbering (Blowers BM)
 - 5.Numbering (Blowers BG)
 - 6.Numbering (FAL)
 - 7.Sensors
 - 8.Speed Control
- AC Fans**
- Technical Information**
- Handling Precautions**
- Quality & Environment**

DC Axial Fans FB Series Part Numbering System

To show details, place the mouse cursor on each item of the part number. Click "Display All" button to :

FB **A** **08** **A** **12** **H** **1** **A** **S**

(1) (2) (3) (4) (5) (6) (7) (8) (9)

1. Motor type

FB DC Axial fans

2. Bearing type or Motor Type

A HWB
K Ball bearing
L ES Series

3. Housing Size

04 40 X 40mm 09
06 60 X 60mm 12
08 80 X 80mm

4. Housing thickness

A	25.5mm	F	20mm
T	15mm	H	42mm
G	38mm		

5. Rated voltage

12	12V
24	24V

6. Speed

L	Low
M	Middle
H	High
V	Variab

7. Terminal

1	With leads
<input type="checkbox"/>	No leads

8. Lead wire

A	Standard 2 leads
B	Standard 3 leads
C~	Optional leads

9. Option

S	Locked ser
X	Tacho sen:
Z	Solid corne
O	S + Z