



T&B Catalog Number: EFC050
UPC Number: 78621078961
Description: 1/2" Black Corrugated PVC flexible tubing.
 For use with Bullet®; Liquidtight Fittings.

Status: Active

Features

- Maximum flexibility in tight applications.
- Extremely fast installation
- Liquidtight with specified fittings.
- Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

General

Material	PVC
Color	Black
Conduit Size (inches)	1/2
Recommended industrial applications	Protection of fiber optic cable, installation of instrumentation and control cable, indoor and outdoor lighting, packaging equipment, marine and ship-board wiring, and flexing-component wiring protection on robots, graphic arts equipments, etc.

Dimension Information

I.D. - Minimum (inches)	.622
I.D. - Maximum (inches)	.642
O.D. - Minimum (inches)	.820
O.D. - Maximum (inches)	.840

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	10.3 lbs. per 100

Application Support

Guide to Nonmetallic Conduit Applications	Available on Website
XTRAFLEX System Specifications	Available on Website

Notes

*Note	OEM Grade U.L. Recognized
**Note	Broad operating temperature range - 18°° C to +60°° C (-28°° F to +140°° F)
***Note	Flammability rating VW-1 (vertical wire) UL 224.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications

File Nbr:
E 96548

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

