



Ty-Fast®

TY400-120X

All-plastic cable tie for multi purpose use. UV-resistant version, especially recommended for outdoor applications.

T&B Catalog Number: TY400-120X
EAN Number: 05414363064527
UPC Number: 78621089827
Description: All-plastic, standard cable tie, 375 x 7.6 mm, black Polyamide 6.6 UV-resistant



Technical Information

Type	standard
Material	Polyamide 6.6 UV-resistant
Temperature Range	-40°C to +85°C
Flammability Rating	UL 94 V-2
Colour	black
Halogen free	yes
Silicone free	yes
UV-resistant	yes

Approvals

UL recognised	E49405
Lloyds Register approval	yes
MIL Spec.	MS-3367-3
Other approval	BVQ

Ordering Information

Length (mm)	375
Width (mm)	7.6
Max. Bundle Diameter (mm)	102
Min. Bundle Diameter (mm)	4.8
Min. Tensile Strength (N)	540
Quantity (pieces)	500
Packaging Type	bag

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG120, L-500-EU, WT3D
