

FRP Polysafe Enclosures with Standard Door

Additional depths available

Up to 2 depth extensions may be added. Includes (4) stainless steel mounting feet



FEATURES

- Designed for wall mounting and free standing units
- Can be coupled in height, width, and depth
- Lexan windows are .236" thick with a neoprene gasket
- Door has a single entry five-point latching system
- Available in pedestal version
- Temperature resistance -58°F to +302°F (-50°C to +150°C)
Momentary to +392°F (200°C)

ACCESSORIES

- Key-lock cylinders and padlockable handles
- Adjustable mounting hardware
- Rainhoods
- Floorpads

Part Number	Outside Dimensions			Inside Dimensions			Weight
	H	W	D	h	w	d	
PS2020A (mm)	19.70 (500)	19.70 (500)	12.60 (320)	16.14 (410)	16.14 (410)	11.25 (286)	25 lb 11.3 kg
PS2030A (mm)	19.70 (500)	29.53 (750)	12.6 (320)	16.14 (410)	25.98 (660)	11.26 (286)	37.5 lb 17 kg
PS3020A (mm)	29.53 (750)	19.70 (500)	12.60 (320)	25.98 (660)	16.14 (410)	11.26 (286)	37.5 lb 17 kg
PS3030A (mm)	29.53 (750)	29.53 (750)	12.60 (320)	25.98 (660)	25.98 (660)	11.26 (286)	43.8 lb 19.8 kg
PS3040A (mm)	29.53 (750)	39.37 (1000)	12.60 (320)	25.98 (660)	35.83 (910)	11.26 (286)	56 lb 25.4 kg
PS3050/2A (mm)	29.53 (750)	49.21 (1250)	12.60 (320)	25.98 (660)	45.66 (1160)	11.26 (286)	69 lb 31.3 kg
PS4020A (mm)	39.37 (1000)	19.70 (500)	12.60 (320)	35.83 (910)	16.14 (410)	11.26 (286)	43.8 lb 19.8 kg
PS4030A (mm)	39.37 (1000)	29.53 (750)	12.60 (320)	35.83 (910)	25.98 (660)	11.26 (286)	56 lb 25.4 kg
PS4040A (mm)	39.37 (1000)	39.37 (1000)	12.60 (320)	35.83 (910)	35.83 (910)	11.26 (286)	69.6 lb 31.5 kg
PS4040/2A* (mm)	39.37 (1000)	39.37 (1000)	12.60 (320)	35.83 (910)	35.83 (910)	11.26 (286)	69.6 lb 31.5 kg
PS4050/2A* (mm)	39.37 (1000)	49.21 (1250)	12.60 (320)	35.83 (910)	45.67 (1160)	11.26 (286)	83.5 lb 37.8 kg
PS5030A (mm)	49.21 (1250)	29.53 (750)	12.60 (320)	45.67 (1160)	25.98 (660)	11.26 (286)	69 lb 31.3 kg
PS5040/2A* (mm)	49.21 (1250)	39.37 (1000)	12.60 (320)	45.67 (1160)	35.83 (910)	11.26 (286)	83.5 lb 37.8 kg
PS5040/2LA* (mm)	49.21 (1250)	39.37 (1000)	12.60 (320)	45.67 (1160)	35.83 (910)	11.26 (286)	83.5 lb 37.8 kg

ADDITIONAL ACCESSORIES AVAILABLE UPON REQUEST

