




General ordering data

Order No.	1608650000
Part designation	ZPE 2.5/3AN
Version	Earth terminal, 2.5 mm ² , Tension clamp connection, Wemid, green/yellow, TS 35
EAN	4008190076559
Qty.	100 pc(s).

Product notes

Product description	Z-series standard ranges provide solutions for conductor cross-sections from 0.05 to 35 mm ² .
---------------------	---

PT OKIECEx/ATEX rating data

EU-type examination certificate	KEMA97ATEX2521U
Download, German	KEMA97ATEX2521U_d.pdf
Download English	KEMA97ATEX2521U_e.pdf
IECEx Certificate of Conformity	IECExULD05.0009U
Download	IECExULD05.0009U_e.pdf
ATEX conductor cross-section	2.5 mm ²
IECEx conductor cross-section	2.5 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	green/yellow
Connection direction	top
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No

Additional technical data

No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	3
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	Z-series
Type of connection	Clamped
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	PE terminal

CSA rating data

Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 12

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	2.5 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.05 mm ²
Clamping range, max.	4 mm ²
Type of connection	Tension clamp connection
2nd type of connection	clamped
Connection direction	top
No. of connections	3
Stripping length	10 mm
Blade size	0.6 x 3.5 mm
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	2.5 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm ²
AWG conductor size, min.	AWG 30
AWG conductor size, max.	AWG 12
AWG conductor size, min.	0.05 mm ²
AWG conductor size, max.	3.31 mm ²

Dimensions

Width	5.1 mm
Height of lowest version	39.5 mm
Length	64.5 mm
TS 35 offset	32.5 mm

PE rating data

PEN function	No
Pollution severity	3
Rated cross-section	2.5 mm ²
Rated impulse withstand voltage to adjacent terminal	8 kV
Rated short-time current	300 A (2.5 mm ²)
Rated voltage for adjacent terminal	800 V
Standards	IEC 60947-7-2

UL rating data

Min. cross-section (UL)	AWG 30
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes

**Downloads**

DXF	20784_ZPE_2.5-3AN_DXF.dxf
STEP	1608650000_20784_ZPE_2.5-3AN_STP.stp

Classifications

ETIM 2.0	EC000901
ETIM 3.0	EC000901
eClass 4.1	27-14-03-05
eClass 5.0	27-14-03-05
eClass 5.1	27-14-03-05

Similar products

Order No.	Part designation	Version
1690000000	ZDK 2.5PE	Earth terminal, 2.5 mm ² , Tension clamp connection, Wemid, green/yellow, TS 35
1608640000	ZPE 2.5	Earth terminal, 2.5 mm ² , Tension clamp connection, Wemid, green/yellow, TS 35
1608660000	ZPE 2.5/4AN	Earth terminal, 2.5 mm ² , Tension clamp connection, Wemid, green/yellow, TS 35