

## Opto-coupler on locking socket profile RS 40

RS 40



| Ordering data     |                    |                    |                        |                                               |
|-------------------|--------------------|--------------------|------------------------|-----------------------------------------------|
| Connection method | Input voltage      | Function indicator | Screw connection (GSE) | Disconnect plug with screw connection (BL/SL) |
|                   | 5 V <sup>2)</sup>  | Yellow LED         | 1118861001             | 1161560000                                    |
|                   |                    |                    |                        |                                               |
|                   | 12 V <sub>0</sub>  | Green LED          | 1118761001             | 1161660000                                    |
|                   |                    |                    |                        |                                               |
|                   | 24 V <sub>-</sub>  | Yellow LED         | 1160961001             | 1161760000                                    |
|                   |                    |                    |                        | 1177860000 <sup>1)</sup>                      |
|                   | 24 V <sub>0</sub>  | Yellow LED         | 1117461001             | 1119460000                                    |
|                   |                    | Green LED          | 8065031001             |                                               |
|                   |                    |                    |                        |                                               |
|                   | 48 V <sub>0</sub>  | Green LED          | 1161061001             | 1161860000                                    |
|                   |                    |                    |                        |                                               |
|                   | 115 V <sub>0</sub> | Green LED          | 1161161001             | 1161960000                                    |
|                   |                    |                    |                        |                                               |
|                   | 230 V <sub>-</sub> | Green LED          | 1161461001             | 1162060000                                    |
|                   |                    |                    |                        |                                               |
|                   | 230 V <sub>-</sub> | Red LED            |                        | 8182690000                                    |
|                   |                    |                    |                        |                                               |

| Connection data                         |  |                           |                           |               |
|-----------------------------------------|--|---------------------------|---------------------------|---------------|
| Insulation stripping length             |  |                           | 7 mm                      | 6 mm          |
| Conductor cross-section                 |  | 0.5...2.5 mm <sup>2</sup> | 0.5...1.5 mm <sup>2</sup> |               |
|                                         |  |                           | AWG 26...14               | AWG 26...16   |
|                                         |  |                           |                           |               |
| Dimensions                              |  |                           |                           |               |
| Mounting width                          |  |                           | 11.2 mm                   | 11.2 mm       |
| Length (perpendicular to mounting rail) |  |                           | 70 mm                     | 74 mm         |
| Height TS/TS 35 x 7.5                   |  |                           | 56 mm/51.5 mm             | 56 mm/51.5 mm |
|                                         |  |                           |                           |               |
|                                         |  |                           |                           |               |

<sup>1)</sup> Output 5 VTTL-compatible

<sup>2)</sup> Conditionally level-compatible