SPC TECHNOLOGY


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC–F005.DWG

REVISIONS									
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	01–08–10	JAG	03–08–10	XXX	16–08–10

DOC. NO. SPC–F005 * Effective: 7/8/02 * DCP No: 1398

RoHS Compliant



Dimensions : Inches

Specifications:

1. Volts : 12
2. Amps : 0.17
3. Watts : 2.04
4. EFC : 2000
5. Filament : C-2F
6. Life : 12000 hours.

Part Number Table

Description	Part Number
T-2 Candelabra Screw Base Lamp	12RC

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
ASH	01–08–10
CHECKED BY:	DATE:
JAG	03–08–10
APPROVED BY:	DATE:
	XXX

DRAWING TITLE: T–2 Candleabra Screw Base Lamp

SIZE	DWG. NO.	ELECTRONIC FILE	REV
XXX		16N7508	A

SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1