SPC TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC–F005.DWG

REVISIONS

| DCP # | REV | DESCRIPTION | DRAWN | DATE | CHECKD | DATE | APPRVD | DATE |
|---|---|---|---|---|---|---|---|---|
| | | | VEE | 01–08–10 | JAG | 02–08–10 | XXX | 16–08–10 |
| | | | | | | | | |

DOC. NO. SPC–F005 * Effective: 7/8/02 * DCP No: 1398

RoHS Compliant




Dimensions : Inches

Specifications:

1. Voltage : 120
2. Wattage : 7
3. Lumens : 46
4. Filament : C-9
5. Life : 3000 hours

Part Number Table

| Description | Part Number |
|---|---|
| C-7 Candelabra Screw Lamp | 7C7/120V |

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

| DRAWN BY: | DATE: |
|---|---|
| VEE | 01–08–10 |
| CHECKED BY: | DATE: |
| JAG | 02–08–10 |
| APPROVED BY: | DATE: |
| XXX | 16–08–10 |

DRAWING TITLE: C–7 Candelabra Screw Lamp

| SIZE | DWG. NO. | ELECTRONIC FILE | REV |
|---|---|---|---|
| XXX | XXX | 16N7540 | A |

SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1