


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F006.DWG

REVISIONS		DOC. NO.	SPC-F006	Effective 7/8/02	Doc No 1308			
DWG #	REV	DESCRIPTION	DRAWN	DATE	CHECKED	DATE	APPROVD	DATE
1570	A	RELEASED	JWM	9/12/03	JN	07/02/08	JN	07/02/08



- NOTES:
- Material: Hook - Low Density Polyethylene (RMS - 249)
Loop - Nylon Knit (RMS - 251)
 - Operating Temp.: 120°F
 - Total Length: 5 Yards (4.57mm)
 - Color: Orange

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	09/12/03
CHECKED BY:	DATE:
Jason Nash	07/02/08
APPROVED BY:	DATE:
Jason Nash	07/02/08

DRAWING TITLE:		Hook and Loop Roll	
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	50N963	SPC5380	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1