





SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F005.DWG

REVISIONS				DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398			
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE
				VEE	06-08-10	JAG	11-08-10
							20-08-10



Dimensions : Inches (mm)

Current (mA)	Maximum Breakdown		Circuit Volts	Series Resistor	Life (Hours)
	Volts (AC)	Volts (DC)			
1.9	95	135	100-125	30k	25000

Note: External Resistor Required

Part Number Table

Description	Part Number
T 1-3/4 Miniature Flanged, Neon Lamp	C9A

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.		TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWING TITLE: T 1-3/4 Miniature Flanged, Neon Lamp	
DRAWN BY:	DATE:	CHECKED BY:	DATE:	SIZE	DWG. NO.
VEE	06-08-10	JAG	11-08-10	XXX	XXX
APPROVED BY:	DATE:	SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1
XXX	20-08-10				
		ELECTRONIC FILE		23C1338	REV A