



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
698	B	DELETED 2 PARTS	DJC	3/8/99	JC	3/9/99	JC	3/9/99
1914	C	Update To RoHS Compliant	EO	5/29/06	HO	5/30/06	HO	5/30/06



RoHS
Compliant

SPC TYPE NO.	SIZE	EXPANDED I.D. MIN		RECOVERED I.D. MAX.		RECOVERED WALL NOMINAL		SPOOL LENGTH
		(IN.)	(mm)	(IN.)	(mm)	(IN.)	(mm)	
3526	3/16	0.187	4.75	0.093	2.36	0.020	0.51	25
3527	1/4	0.250	6.35	0.125	3.18	0.025	0.64	25
3528	3/8	0.375	9.53	0.187	4.75	0.025	0.64	25
3529	1/2	0.500	12.70	0.250	6.35	0.025	0.64	25
3538	3/16	0.187	4.75	0.093	2.36	0.020	0.51	100
3539	1/4	0.250	6.35	0.125	3.18	0.025	0.64	100
3540	3/8	0.375	9.53	0.187	4.75	0.025	0.64	100
3541	1/2	0.500	12.70	0.250	6.35	0.025	0.64	100
3564	1/16	0.063	1.60	0.031	0.79	0.017	0.43	25
3565	3/32	0.093	2.36	0.046	1.17	0.020	0.51	25
3566	1/8	0.125	3.18	0.062	1.58	0.020	0.51	25
3568	1/16	0.063	1.60	0.031	0.79	0.017	0.43	100
3569	3/32	0.093	2.36	0.046	1.17	0.020	0.51	100
3570	1/8	0.125	3.18	0.062	1.58	0.020	0.51	100

SPECIFICATIONS

USP XXII, NF XVII, CLASS VI Biological Compatibility for Plastics

MATERIAL: Acrylated Polyolefin

CONTINUOUS OPERATING TEMPERATURE RANGE: -55°C to 121°C

MIN. RECOMMENDED SHRINK TEMPERATURE: 121°C (250°F)

COLOR: White

LONGITUDINAL SHRINKAGE: ±5%

CHEMICAL RESISTANCE: Resists a wide range of chemicals

such as Hexachlorophene (pHisoHex), Saline Solution,

Povidone-Iodine (Betadine), Benzalkonium (Zephiran), Alcohol,

as well as moisture, sunlight and fungus

Compatible with all of the following sterilization techniques:

- * Radiation Sterilization (Electron Beam and Gamma)
- * ETO Sterilization (Low ETO residuals with only 3 day aeration)
- * Steris Process (Paracetic Acid)
- * Hydrogen Peroxide Gas
- * Glutaraldehyde
- * Autoclave Sterilization (20 cycles @121°C, 15 psig for 156 min. with a fast dry cycle)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

DANIEL CAREY

DATE:

5/20/98

CHECKED BY:

JOHN COLE

DATE:

6/11/98

APPROVED BY:

JEFF MCVICKER

DATE:

6/11/98

DRAWING TITLE:

MEDICAL GRADE HEAT SHRINK

SIZE

A

DWG. NO.

TA-129

ELECTRONIC FILE

TA-129.DWG

REV

C

SCALE: NTS

U.O.M.: INCHES

SHEET: 1 OF 2

PROPERTY	TEST METHOD	TYPICAL VALUE
SPECIFIC GRAVITY	ASTM D792	0.93
TENSILE STRENGTH	ASTM D638	3,200/3,600 psi
ULTIMATE ELONGATION	ASTM D638	500/600%
SECANT MODULUS, @ 2% STRAIN	ASTM D2671	12,000
DUROMETER, Shore A 15 Second Delay	ASTM D2240	53
VOLUME RESISTIVITY @ 500 volts	ASTM D257	$>10^{16}$ ohm-cm @ 500 volts
DIELECTRIC STRENGTH in air @ 500kv/min rise	ASTM D149	1,800/2,000 vpm
DIELECTRIC CONSTANT @ 1MHz	ASTM D150	2.0/2.2
DISSIPATION FACTOR @ 1MHz	ASTM D257	0.008
TOXICITY	40 CFR 798.1175	non-toxic

AUTOCLAVE CYCLE TEST

20 cycles @ 121°C 15 psig for 15 min with fast dry cycle followed by test for:

PROPERTY	TEST METHOD	TYPICAL VALUE
VOLUME RESISTIVITY @ 500 volts		No change from original
DIELECTRIC STRENGTH IN AIR @ 500 kv/min rise	ASTM D 149	No change from original
DIELECTRIC CONSTANT @ 1MHz	ASTM D 150	No change from original
DISSIPATION FACTOR @ 1MHz	ASTM D 150	No change from original