



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC-F005.DWG

## REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

| DCP # | REV | DESCRIPTION             | DRAWN | DATE    | CHECKD | DATE    | APPRVD | DATE    |
|-------|-----|-------------------------|-------|---------|--------|---------|--------|---------|
| 1125  | B   | UPDATED TO TABULAR SPEC | HYO   | 3/16/01 | JC     | 5/17/01 | JC     | 5/17/01 |
| 1848  | C   | Update Tolerance        | HO    | 7/1/05  | JWM    | 7/1/05  | JWM    | 7/1/05  |

| SPC TYPE NO.  | Thickness (Inches) | O.D. (Inches)   | Screw Size |
|---------------|--------------------|-----------------|------------|
| WLI-02-012-SC | (0.010 - 0.015)    | (0.175 - 0.200) | 2          |
| WLI-04-017-SC | (0.015 - 0.019)    | (0.255 - 0.270) | 4          |
| WLI-06-018-SC | (0.017 - 0.021)    | (0.275 - 0.295) | 6          |
| WLI-08-021-SC | (0.018 - 0.023)    | (0.325 - 0.340) | 8          |
| WLI-10-024-SC | (0.020 - 0.025)    | (0.365 - 0.381) | 10         |
| WLI-25-030-SC | (0.023 - 0.028)    | (0.460 - 0.478) | 1/4        |
| WLI-24-044-SC | (0.032 - 0.040)    | (0.670 - 0.692) | 3/8        |



**MATERIAL:** Spring Steel, Zinc Plated

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

### TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

J.C.

CHECKED BY:

APPROVED BY:

DATE:

9/10/91

DATE:

DATE:

DRAWING TITLE:

INTERNAL TOOTH LOCKWASHERS

SIZE

A

DWG. NO.

TA-306

ELECTRONIC FILE

TA-306.DWG

REV

C

SCALE: NTS

U.O.M.: INCHES

SHEET: 1 OF 1