
ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

RoHS Compliant

REVISIONS			DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1979	A	RELEASED	JWM	2/14/00	JN	03/17/08	JN	03/17/08



SPC #	Cable	Length	Strain Relief
SPC20676	RG-55B/U	12	No
SPC20677	RG-55B/U	24	No
SPC20678	RG-55B/U	36	No
SPC20679	RG-55B/U	48	No
SPC20680	RG-55B/U	60	No
SPC20681	RG-55B/U	72	No
SPC20682	RG-62A/U	36	No
SPC20683	RG-62A/U	48	No
SPC20684	RG-62A/U	60	No
SPC20781	RG-58A/U	12	Yes
SPC20782	RG-58A/U	48	Yes
SPC20783	RG-58A/U	60	Yes
SPC20784	RG-58A/U	72	Yes
SPC20785	RG-58C/U	12	No
SPC20786	RG-58C/U	36	No
SPC20787	RG-58C/U	60	No
SPC20788	RG-58C/U	72	No
SPC20872	RG-59B/U	12	No
SPC20789	RG-62A/U	36	No
SPC20790	RG-62A/U	72	No
SPC20791	RG-142B/U	12	No
SPC20792	RG-142B/U	24	No
SPC20793	RG-142B/U	36	No
SPC20794	RG-174A/U	36	No
SPC20795	RG-174A/U	60	No
SPC20796	RG-223/U	24	No
SPC20797	RG-223/U	36	No
SPC20798	RG-223/U	48	No
SPC20799	RG-223/U	60	No
SPC20800	RG-223/U	72	No
SPC20801	RG-316/U	72	No

* SEE CHART

** DUAL WALL POLYOLEFIN

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH
4	CABLE	1	SEE CHART	VARIOUS
3	TUBING	*	**HEAT SHRINK	BLACK
2	STRAIN RELIEF	*	POLYVINYL CHLORIDE	BLACK
1	BNC MALE CRIMP	2	BRASS	NICKEL

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	2/14/00
CHECKED BY:	DATE:
Jason Nash	03/17/08
APPROVED BY:	DATE:
Jason Nash	03/17/08

DRAWING TITLE: CABLE ASSEMBLY
BNC Male, Crimp, to BNC Male, Crimp

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-867	TA-867.DWG	A

SCALE: NTS | U.O.M.: INCHES [mm] | SHEET: 1 OF 1