


REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1934	A	Released	JN	07/29/08	JWM	07/29/08	JWM	07/29/08



Notes:

1. New product shall be reference to Ballcore GR-326 standard.
2. Insertion loss: <=0.2dB typical (1300nm).
3. Cable Marking: Key Optics! MMF-62.5/125 optical fiber cable  
OFNR(UL) E241104 0611 \*\*\*\*\*M

SPC #	Length (Meters)
SPC22822	1
SPC22823	2
SPC22824	3
SPC22825	5
SPC22826	10

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	07/29/08
CHECKED BY:	DATE:
JWM	07/29/08
APPROVED BY:	DATE:
JWM	07/29/08

DRAWING TITLE: 62.5 SIMPLEX SC/SC 1M			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	Ta-898	Ta-898.DWG	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	