

### Connector/Cable Cross Reference Guide

Cable Part#	"F"			BNC			RCA		
									
<b>25-26 AWG</b> Center Conductor: .015 ~ .025 Dielectric: .065 ~ .078 Outer Jacket: .095 ~ .110	1277P	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1277R	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1278R	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1279P	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1279R	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1280P	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1280R	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1281R	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1281S3	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1281S5	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1281S6	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1282S3	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1282S5	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1282S6	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
	1283S3	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA
1283S5	-	-	-	FS1BNC	DB1BNC DB1BNCHD	-	FS1RCA	DB1RCA	
<b>22-24 AWG</b> Center Conductor: .015 ~ .025 Dielectric: .095 ~ .105 Outer Jacket: .145 ~ .160	1164B	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	1406B	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	1407B	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	1417B	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	1418B	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	1855A	SNSFMB	FS15	-	FS15BNC	1855ABHD1 1855ABHDL	-	FS15RCA	DB15RCA
	1855S3	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	1855S5	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	573945	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	673948	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7787A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7788A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7789A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7790A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7791A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7792A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	7796A	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA
	8218	-	FS15	-	FS15BNC	DB15BNCHD	-	FS15RCA	DB15RCA

Connector/Cable Cross Reference Guide

Cable Part#	"F"			BNC			RCA		
									
1153A	-	FS11V		-	FS11BNC		-	-	-
1523A	SNS1P11	FS11V, FS11RA		-	FS11BNC		-	-	-
1525A	SNS1P11	FS11V		-	FS11BNC		-	-	-
1617A	SNS1P11	FS11V		-	FS11BNC		-	-	-
1618A	SNS1P11	FS11V		-	FS11BNC		-	-	-
513945	SNS1P11		-	-		-	-	-	-
613948	-	FS11PL		-		-	-	-	-
6139B8	-	FS11PL		-		-	-	-	-
7731A	SNS1P59	FS11V, FS11RA	-	-	FS11BNC	FS11BNC	-	-	-
7732A	-	FS11PL	-	-	-	-	-	-	-
7983A	SNS1P11	FS11V	FS11V	-	FS11BNC		-	-	-
8213	-	FS11V, FS11RA	-	-	FS11BNC	-	-	-	-
9011	SNS1P11	FS11V	FS11V	-	FS11BNC		-	-	-
9064	SNS1P11	FS11V, FS11RA		-	FS11BNC		-	-	-
9292	SNS1P11	FS11PL	-	-	-	-	-	-	-
9764	SNS1P11	FS11V		-	FS11BNC		-	-	-

RG11  
Center Conductor: .0634 ~ .0647  
Dielectric: .280 ~ .294  
Outer Jacket: .390 ~ .417

Cable Part#	"F"			BNC			RCA		
									
1186A	SNS1P59U, SNS1P59QS	FS59U	DB59U	SNS1P59QSBNC	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
1426A	SNS1P59	-	-		FS59BNC SL	DB59BNC SL		FS59RCASL	DB59RCASL
1505A	SNS1P59	FS59U	DB59U		FS59BNCU	DB59BNCU DB59BNC HD 1505ABHD1 1505ABHDL		FS59RCAU	DB59RCAU
1505F	-	FS59U	DB59U		FS59BNCU	DB59BNCU DB59BNC HD 1505ABHD1 1505ABHDL		FS59RCAU	DB59RCAU
1505S3	-	FS59U	DB59U		FS59BNCU	DB59BNCU DB59BNC HD 1505ABHD1 1505ABHDL		FS59RCAU	DB59RCAU
1505S5	-	FS59U	DB59U		FS59BNCU	DB59BNCU DB59BNC HD 1505ABHD1 1505ABHDL		FS59RCAU	DB59RCAU
1505S6	-	FS59U	DB59U		FS59BNCU	DB59BNCU DB59BNC HD 1505ABHD1 1505ABHDL		FS59RCAU	DB59RCAU
1506A	-	FS59PL2	DB59PL2/4		FS59BNC PL2	DB59BNC PL2/4		FS59RCAPL2	DB59RCAPL2/4
543945	-	FS59U	DB59U	SNSB59A	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
549945	-	FS59U	DB59U	SNSB59A	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
643948	-	FS59PL2	DB59PL2/4	SNSB59PB	FS59BNC PL4	DB59BNC PL2/4		FS59RCAPL2	DB59RCAPL2/3/4
6439C8	-	FS59PL2	DB59PL2/4	-	FS59BNC PL2	DB59BNC PL2/4		FS59RCAPL2	DB59RCAPL2/3/4
649948	-	FS59PL2	DB59PL2/4	SNSB59PB	FS59BNC PL2	DB59BNC PL2/4		FS59RCAPL2	DB59RCAPL2/3/4
82108	-	FS59U	DB59U		FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
8212	-	-	-		FS59BNC SL	DB59BNC SL		FS59RCASL	DB59RCASL
8221	SNS1P59	-	-		-	DB59BNC BU		-	-
82241	-	-	-		FS59BNC PL3	DB59BNC PL3		FS59RCAPL3	DB59RCAPL2/3/4
82259	-	FS59PL2	DB59PL2/4		FS59BNC PL2	DB59BNC PL2/4		FS59RCAPL2	DB59RCAPL2/3/4
8241	SNS1P59	-	-		-	DB59BNC BU		-	-
8241A	-	-	-		-	DB59BNC BU		-	-
8241B	-	-	-		-	DB59BNC BU		-	-
8241F	-	-	-		-	DB59BNC BU		-	-
8263	SNS1P59	FS59U	DB59U		FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
8279	-	FS59PL	-		FS59BNC PL	-		FS59RCAPL	-
8281	-	-	-		-	DB59SL2-M, DB59SL2-F		-	-
8281B	-	-	-		-	DB59SL2-M, DB59SL2-F		-	-
88241	-	-	-		FS59BNC PL3	DB59BNC PL3		FS59RCAPL3	DB59RCAPL2/3/4
89108	-	FS59PL4	DB59PL2/4		FS59BNC PL4	DB59BNC PL2/4		FS59RCAPL4	DB59RCAPL2/3/4
9100	SNS1P59 SNS1P59U	FS59U	DB59U	SNS1P59BNC	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
9104	SNS1P59 SNS1P59U	FS59U	DB59U	SNS1P59BNC	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
9104P	-	FS59U	DB59U	-	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
9167	SNS1P59 SNS1P59U	FS59U	DB59U	SNS1P59BNC	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
9240	SNS1P59	-	-		FS59BNC SL	DB59BNC SL		FS59RCASL	FS59RCASL
9244	SNS1P59	FS59U	DB59U		FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
9259	-	FS59U	DB59U		FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU
9275	SNS1P59 SNS1P59U	FS59U	DB59U	SNS1P59BNC	FS59BNCU	DB59BNCU		FS59RCAU	DB59RCAU

RG59  
Center Conductor: .0317 ~ .0339  
Dielectric: .144 ~ .157  
Outer Jacket: .232 ~ .273



1152A	-	FS6U	DB6U			FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1189A	SNC6U SNS1P6QS, SNS1P6U	FS6U	DB6U		SNS1P6QSBNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1189AP	-	FS6U	DB6U		-	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1190A	SNC6U SNS1P6QS, SNS1P6U	FS6U	DB6U		SNS1P6QSBNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1530A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1532A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1545A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1546A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1613A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1614A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1694A	SNS1P6	FS6U	DB6U			FS6BNCU	DB6BNCU DB6BNCU 1694ABHD1 1694ABHD1		FS6RCAU	DB6RCAU
1695A	-	FS6PL2	DB6PL2			FS6BNCPL2	DB6BNCPL2 1695ABHD1 1695ABHD1		FS6RCAPL2	DB6RCAPL2
1829A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1829AC	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1829P	SNS6PLB	FS6PL2	DB6PL2		-	FS6BNCPL2	DB6BNCPL2		FS6RCAPL2	DB6RCAPL2
1829R	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1840A	-	FS6U	DB6U		-	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1841A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1841AC	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
1843A	-	FS6U	DB6U		-	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
533945	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
5339B5	-	FS6U	DB6U		-	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
5339Q5	SNC6U SNS1P6QS, SNS1P6U	FS6U	DB6U		SNS1P6QSBNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
5339W5	-	FS6U	DB6U		-	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
5399B5	-	FS6U	DB6U		-	FS6BNCU	DB6BNCU		FS6RCAPL2	DB6RCAPL2
633938	-	FS6PL2	DB6PL2		-	FS6BNCPL2	DB6BNCPL2		FS6RCAPL2	DB6RCAPL2
633948	-	FS6PL2	DB6PL2		-	FS6BNCPL2	DB6BNCPL2		FS6RCAPL2	DB6RCAPL2
6339Q8	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
639948	-	FS6PL2	DB6PL2		-	FS6BNCPL2	DB6BNCPL2		FS6RCAPL2	DB6RCAPL2
7710A	SNS1P6	FS6U	DB6U			FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
7711A	SNS1P6	FS6U	DB6U			FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
7712A	SNS1P6	FS6U	DB6U			FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
7713A	SNS1P6	FS6U	DB6U			FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
7915A	SNS1P6 SNS1P6U, SNC6U	FS6U	DB6U		SNS1P6BNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
7916A	SNC6U SNS1P6QS, SNS1P6U	FS6U	DB6U		SNS1P6QSBNC	FS6BNCU	DB6BNCU		FS6RCAU	DB6RCAU
82120	-	FS6PL2	DB6PL2			FS6BNCPL2	DB6BNCPL2		FS6RCAPL2	DB6RCAPL2
82248	-	FS6PL2	DB6PL2			FS6BNCPL2	DB6BNCPL2		FS6RCAPL2	DB6RCAPL2

RG6  
Center Conductor: .0399 ~ .0418  
Dielectric: .180 ~ .193  
Outer Jacket: .265 ~ .305

## Connector/Cable Cross Reference Guide

Cable Part#	"F"			BNC			RCA		
	 SNSUTL	 CPLCCT-XXX*	 CPLCRBC-BR	 SNSUTL	 CPLCCT-XXX*	 CPLCRBC-BR	 SNSUTL	 CPLCCT-XXX*	 CPLCRBC-BR
89120	-	FS6PL2	DB6PL2	-	FS6BNCPL2	DB6BNCPL2	-	FS6RCAPL2	DB6RCAPL2
89248	-	FS6PL2	DB6PL2	-	FS6BNCPL2	DB6BNCPL2	-	FS6RCAPL2	DB6RCAPL2
9058	SNS1P6 SNS1P6U_SNC6U	FS6U	DB6U	SNS1P6BNC	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9062	SNS1P6 , SNS1P6U SNC6U	FS6U	DB6U	SNS1P6BNC SNSRM6xx	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9066	SNS1P6 SNS1P6U_SNC6U	FS6U	DB6U	SNS1P6BNC	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9077	SNS1P6 , SNS1P6U SNC6U	FS6U	DB6U	SNS1P6BNC SNSRM6xx	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9116	SNS1P6 SNS1P6U_SNC6U	FS6U	DB6U	SNS1P6BNC	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9116P	SNS6PLA	FS6PL2	DB6PL2	-	FS6BNCPL2	DB6BNCPL2	-	FS6RCAPL2	DB6RCAPL2
9116R	-	FS6U	DB6U	-	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9118	SNS1P6 SNS1P6U_SNC6U	FS6U	DB6U	SNS1P6BNC	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9248	SNS1P6	FS6U	DB6U	-	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU
9290	-	FS6U	DB6U	-	FS6BNCU	DB6BNCU	-	FS6RCAU	DB6RCAU

\*CPLCCT-XXX is the root part number for the following tools (CPLCCT-SLM = 59/6/RGB connectors, CPLCCT-SS59/11 = RG11 connectors)