



DURATOOL		
SPC Type No.: MC35757		
Desc.: FLOOR MAT, 2 LAYER RUBBER, 48" x 72" GROUND CORD, UNIVERSAL SNAP KIT		
Qty & UOM:	QTY EA	2010-07-14 EMP
RoHS Compliant: No	Tracking Info: RPXXXXXXXXX Made in USA.	

Packaging Label

SPECIFICATIONS:

Mat:

Construction: Dual layer rubber material

- Static Dissipative top layer
- Conductive rubber bottom layer

Material Thickness: .060" (± 10%)

Color: Blue

Texture: Smooth

Dissipative Color Side:

- RTT: 10E6 - 10E8 ohms per ANSI/ESD S4.1
- RTG: 10E6 - 10E8 ohms per ANSI/ESD S4.1

"Slows charge removal; meets minimum recommended work surface requirements of ANSI/ESD S20.20 and recommendations of STM 4.1"

Ground Cord:

Length: 15'

Terminations: 10mm male stud snap, ring terminal

Resistor: 1 megohm

Universal Snap Kit:

Size: 10mm

Kit Includes: 10mm stud snap, 10mm socket snap, threaded backing washer, long screw, short screw, & groundable point label

PACKAGING:

Product to be packaged with Duratool label

Tolerances:
Width: ± 0.250"
Length: ± 0.250" every 1 linear foot of running material

Special manufactured items are not returnable for credit  MADE IN AMERICA

CUSTOMER APPROVAL	DATE
-------------------	------

FLOOR MAT, 2 LAYER RUBBER, 48" x 72", GROUND CORD, UNIVERSAL SNAP KIT, PACK WITH DURATOOL LABEL, MC35757



3651 WALNUT AVE., CHINO, CA 91710
PHONE (909) 627-9634 FAX (909) 363-7322
WEBSITE: www.CMG-Sales.com

DRAWING NUMBER	DATE
CMG-10744	July 2010