



Packaging Label

### SPECIFICATIONS:

#### Mat:

- Construction: Dual layer rubber material
  - Static Dissipative top layer
  - Conductive rubber bottom layer

Material Thickness: .060" (± 10%)

Color: Grey

Texture: Smooth

#### Dissipative Color Side:

- RTT: 10E6 - 10E8 ohms per ANSI/ESD S4.1
- RTG: 10E6 - 10E8 ohms per ANSI/ESD S4.1

*"Slows charge removal; meets minimum recommended work surface requirements of ANSI/ESD S20.20 and recommendations of STM 4.1"*

#### Wrist Strap:

Construction: Soft elastic band with silver impregnated polypropylene on the inside for reliable removal of static charge

Snap: 4mm male stud snap

Cord Length: 6'

Cord Terminations: 4mm socket snap, molded banana plug

#### Ground Cord:

Length: 15'

Terminations: 10mm male stud snap, ring terminal

Resistor: 1 megohm

#### Universal Snap Kit:

Size: 10mm

Kit Includes: 10mm stud snap, 10mm socket snap, threaded backing washer, long screw, short screw, & groundable point label

#### PACKAGING:

Product to be packaged with Duratool label



MADE IN AMERICA

Tolerances:  
Width: ± 0.250"  
Length: ± 0.250" every 1 linear foot of running material

Special manufactured items are not returnable for credit

<p>CUSTOMER APPROVAL _____ DATE _____</p>	<p>BENCH TOP MAT, 2 LAYER RUBBER, 24" x 48", WRIST STRAP, ADJ ELASTIC, 6' COIL CORD, GROUNDING CORD, UNIVERSAL SNAP KIT, PACK WITH DURATOOL LABEL, MC35758</p>		
<p><b>CMG</b></p>	<p>3651 WALNUT AVE., CHINO, CA 91710 PHONE (909) 627-9634 FAX (909) 363-7322 WEBSITE: www.CMG-Sales.com</p>	<p><b>DRAWING NUMBER</b> CMG-10745</p>	<p><b>DATE</b> July 2010</p>