





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	25-10-10	JAG	xxx	xxx	02-11-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



Dimensions : Inches (mm)

NOTE

Fans : 3 X 105 cfm, ball bearing
 115V, 50/60Hz, 0.21A
 UL/CE
 Fan Guards : Steel C1010, Nickel Chrome Plated
 UL spacing
 Pre-wired: SPT-118/2

Part Number Table

Description	Part Number
Fan Tray Module	MC33040

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY: ASH
 CHECKED BY: JAG
 APPROVED BY: xxx

DATE: 25-10-10
 DATE: xxx
 DATE: 02-11-10

Fan Filter

SIZE	DWG. NO.	ELECTRONIC FILE
A	MC33040	87P0762
SCALE: NTS	U.O.M.: Millimeters	SHEET: 1 OF 1

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.