





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	25-10-10	JAG	XXX	XXX	02-11-10

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398



**Note:**  
 Fans: 3 X 105 cfm, ball bearing  
 230 V, 50/60 Hz, 0.1 Amp  
 UL/CE  
 Power Cord: 6 feet, 18/3 SJT with  
 Strain Relief  
 Nema 6-15P  
 Fan Guards: Steel C1010  
 Nickel Chrome Plated  
 UL Spacing  
 Pre-Wired: SPT-1 18/2 Expandable with  
 Part # MC33042, 6 or 9  
 Fans

Part Number Table

Description	Part Number
Complete Fan Tray Assembly	MC33041

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

ASH

DATE:

25-10-10

DRAWING TITLE:

Complete Fan Tray Assembly

CHECKED BY:

JAG

ELECTRONIC FILE

87P0763

DATE:

XXX

REV

A

APPROVED BY:

XXX

SCALE:

NTS

SHEET:

1 OF 1

DISCLAIMER:  
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

DRAWN BY:	DATE:
CHECKED BY:	DATE:
APPROVED BY:	DATE:
XXX	02-11-10

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	MC33041	87P0763	A
SCALE:	U.O.M.: Millimeters	SHEET:	1 OF 1
NTS			