

#### **ARIA ACCESSORIES**

#### **Mounting Hardware**

**AN-MFSS** 

set of 4 mtg feet 304 stainless steel



**AN-NMF** 

set of 4 mtg feet in polyamide (non-metallic)







interchangeable (supplied with 1 key)

**KLC-SP** 

.12 (3mm)

**KLC-SQ8** 

.31 (8 mm)

KLC-T8

.31 (8mm)

KLC-T11

**KLC-DB3** 

.43 (11mm) .12 (3 mm)

Other locks on request

## **Handles**

# A-HN

neutral handle



### A-HKL

Small keylock handle 2 keys 2432E



#### A-HNM

Semi-flush neutral handle



# A-HNMKL

A-HNMPL

Semi-flush keylock handle Key cylinder lock included



Semi-flush padlockable handle



#### Ventilators

#### RDV

Set of two ventilation grids

Mtg. Hole Ø 1.40" Color: White




## **Hinge supports**

#### AFPH

set of 2 hinge supports for cover plate




#### **Usable Space**



Large	Enclosure	Height	Small
	(H)	Side (S)	Side (L)
AN1208	5	4.25	7.25
AN1612	5.5	7	11
AN2016	7.5	11	15
AN2416	7.5	11	19
AN2820	8.5	15	20.25
AN3325	9.75	19	24

# ABP-DA

Set of 4 back plate depth adjusters



## **Pressure Compensation Plug**

#### **PCP**

Polycarbonate/ABS plug Mtg. Hole Ø 1.50" Color: Beige





# **Document pocket** - DIN A4

Self-adhesive

1021.020 (PPS) 1031.010 (PPD) 8.27 x 5.12 x .50 9.00 x 8.50 x 1.00 Color: Beige



# **Carrying Handle**

**41270.070 (CH)** Height 1.97

Width reinforcement rib + screws Made of Vyncolite Color: Black



#### Air vents

Two air vents must be mounted per enclosure to ensure sufficient air circulation and prevent condensation water. Complete with template and screws. Air vents are preferably mounted in the upper and lower part of the base.

#### **10000.010 (MEDV)** Set of 2 pieces in

polyamide Color: Grey



#### **SEDV**

Small drain vent set of 2 pieces in polyamide Color: Grey

