



General ordering data

Order No.	0409600000
Part designation	H0,75/12 W
Version	Wire-end ferrule, 0.75 mm ² , 6 mm, Colour code: Weidmüller, white
EAN	4008190079826

Technical data

Length	12 mm
Width	3.3 mm
Height	3.3 mm

Product data

Conductor rated cross-section	0.75 mm ²
AWG	18
Total length (L1)	12 mm
Contact surface length (L2)	6 mm
Contact surface diameter (D1)	1.2 mm
Collar diameter (D2)	2.8 mm
Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm

Approvals

Approvals institutes



Classifications

eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01
eClass 5.1	27-40-02-01

Similar products

Order No.	Part designation	Version
9019030000	H0,75/12D GR	Wire-end ferrule, 0.75 mm ² , 6 mm, Colour code: DIN, grey
9021030000	H0,75/12T HBL	Wire-end ferrule, 0.75 mm ² , 6 mm, Colour code: Miscellaneous, light blue
9021040000	H0.75/14 HBL	Wire-end ferrule, 0.75 mm ² , 8 mm, Colour code: Miscellaneous, light blue
0462900000	H0,75/14 W	Wire-end ferrule, 0.75 mm ² , 8 mm, Colour code: Weidmüller, white
9019040000	H0,75/14D GR	Wire-end ferrule, 0.75 mm ² , 8 mm, Colour code: DIN, grey
9025860000	H0,75/16 W	Wire-end ferrule, 0.75 mm ² , 10 mm, Colour code: Weidmüller, white
9019050000	H0,75/16D GR	Wire-end ferrule, 0.75 mm ² , 10 mm, Colour code: DIN, grey
9021050000	H0,75/16T HBL	Wire-end ferrule, 0.75 mm ² , 10 mm, Colour code: Miscellaneous, light blue
9025910000	H0,75/18 W	Wire-end ferrule, 0.75 mm ² , 12 mm, Colour code: Weidmüller, white
9019060000	H0,75/18D GR	Wire-end ferrule, 0.75 mm ² , 12 mm, Colour code: DIN, grey
9021060000	H0,75/18T HBL	Wire-end ferrule, 0.75 mm ² , 12 mm, Colour code: Miscellaneous, light blue