





REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2055	A	RELEASED	JN	06/15/09	JWM	06/15/09	JWM	06/15/09



**SPECIFICATIONS**

- CURRENT: 0.5A/ CONTACT
- VOLTAGE: 30VAC/ CONTACT
- LOW LEVEL CONTACT RESISTANCE: 80 MOHM MAX.
- MATING FORCE: MAXIMUM OF 55.5N
- UNMATING FORCE: MAXIMUM OF 49.0N
- OPERATING TEMPERATURE: -20°C to +85°C
- CONTACT & CONNECTION TYPE: SOCKET
- NUMBER OF PIN: 36 POSITIONS
- CONTACT PLATING: 15U" GOLD OVER NICKEL,  
SOLDER AREA PLATING TIN
- SHELL PLATING: NICKEL PLATED

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

**TOLERANCES:**  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	06/15/09
CHECKED BY:	DATE:
Jeff McVicker	06/15/09
APPROVED BY:	DATE:
Jeff McVicker	06/15/09

DRAWING TITLE:			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	61U036S-320N-B	06R5636.dwg	A
SCALE:	NTS	U.O.M.: Millimeters	SHEET: 1 OF 2

