






DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1269	A	RELEASED	JWM	12/2/02	HO	12/2/02	DJC	12/2/02
1811	B	RoHS ADDED	DCM	12/22/05	JWM	12/22/05	JWM	12/22/05



Material:

Housing: Thermoplastic
Terminal: Copper Alloy

Characteristics:

Rating: 15A 250V AC
Insulation Resistance: Over 100 MegOhm 500VDC
Dielectric Strength: 2000VAC One Minute
Approvals: UL, CSA
Rating: 10A, 250VAC
VDE, SEMKO, DEMKO,
NEMKO, SETI, CB and SEV, FIMKO

SPC-F004.DWG

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	12/2/02
CHECKED BY:	DATE:
Hisham Odish	12/2/02
APPROVED BY:	DATE:
Daniel Carey	12/2/02

DRAWING TITLE:

Snap-In AC Power Outlet IEC 320 - C13

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	2155	92N4158	B
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1