




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2091	A	RELEASED	JYC	4/6/10	JYC	4/6/10	JYC	4/6/10



Material: Nylon



Natural		Black		Length		Width		Max. Bundle Dia		Min. Tensile Strength
Pack 100	Pack 1000	Pack 100	Pack 1000	m.m.	inch	m.m.	Inch	m.m.	Inch	lbs(kgs)
SPC35190	SPC35211	SPC35224	SPC35245	80	3.125	2.4	.093	16	.625	18 (8)
SPC35191	SPC35212	SPC35225	SPC35246	100	4	2.5	.093	22	.859	18 (8)
SPC35192	SPC35213	SPC35226	SPC35247	142	5.5	2.5	.093	35	1.375	18 (8)
SPC35193	SPC35214	SPC35227	SPC35248	165	6.5	2.5	.093	43	1.687	18 (8)
SPC35194	SPC35215	SPC35228	SPC35249	203	8	2.5	.093	55	2.156	18 (8)
SPC35195	SPC35216	SPC35229	SPC35250	142	5.5	3.2	.125	34	1.344	40 (18)
SPC35196	SPC35217	SPC35230	SPC35251	203	8	3.2	.141	53	2.093	40 (18)
SPC35197	SPC35218	SPC35231	SPC35252	250	10	3.6	.141	68	2.672	40 (18)
SPC35198	SPC35219	SPC35232	SPC35253	292	11.5	3.6	.141	82	3.25	40 (18)
SPC35203	N/A	SPC35237	N/A	300	11.8	4.8	.187	83	3.27	40 (18)
SPC35199	N/A	SPC35233	N/A	368	14.5	3.6	.141	105	4.125	40 (18)
SPC35200	SPC35220	SPC35234	SPC35254	160	6.25	4.8	.187	39	1.531	50 (22)
SPC35201	SPC35221	SPC35235	SPC35255	190	7.5	4.8	.187	49	1.922	50 (22)
SPC35202	SPC35222	SPC35236	SPC35256	203	8	4.6	.187	52	2.203	50 (22)
SPC35204	N/A	SPC35238	N/A	368	14.5	4.8	.187	105	4.125	50 (22)
SPC35205	N/A	SPC35239	N/A	450	17.75	4.8	.187	131	5.156	50 (22)
SPC35206	N/A	SPC35240	N/A	550	21.687	4.8	.187	162	6.375	50 (22)
SPC35207	SPC35223	SPC35241	SPC35257	203	8	7.6	.297	52	2.045	120 (55)
SPC35208	N/A	SPC35242	N/A	300	11.875	7.6	.297	80	3.141	120 (55)
SPC35209	N/A	SPC35243	N/A	380	15	7.6	.297	105	4.125	120 (55)
SPC35210	N/A	SPC35244	N/A	450	17.75	8	.312	128	5.032	175 (80)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
JYC	4/6/2010
CHECKED BY:	DATE:
JYC	4/6/2010
APPROVED BY:	DATE:
JYC	4/6/2010

DRAWING TITLE:			
Standard Cable Tie			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-1222	TA-1222.dwg	A
SCALE: NTS		U.O.M.: mm [INCHES]	SHEET: 1 OF 1