





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2091	A	RELEASED	JYC	4/7/10	JYC	4/7/10	JYC	4/7/10



Designed for high-temperature applications in severe environmental conditions



SPC Part Number	Length		Width		Max. Bundle Dia.		Min Tensile Strength		Package
	mm	Inch	mm	Inch	mm	Inch	(kgs)	lbs.	
SPC35395	127	5.0	4.6	.187	25	1.0	100	220	100pcs
SPC35309	201	7.9	4.6	.187	51	2.0	100	220	
SPC35310	266	10.5	4.6	.187	69	2.7	100	220	
SPC35311	300	11.8	4.6	.187	80	3.2	100	220	
SPC35312	362	14.3	4.6	.187	102	4.0	100	220	
SPC35313	521	20.5	4.6	.187	152	6.0	100	220	
SPC35314	127	5.0	7.9	.312	25	1.0	250	550	100pcs
SPC35315	201	7.9	7.9	.312	51	2.0	250	550	
SPC35316	266	10.5	7.9	.312	69	2.7	250	550	
SPC35317	300	11.8	7.9	.312	80	3.2	250	550	
SPC35318	362	14.3	7.9	.312	102	4.0	250	550	
SPC35319	521	20.5	7.9	.312	152	6.0	250	550	

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
JYC	4/7/2010
CHECKED BY:	DATE:
JYC	4/7/2010
APPROVED BY:	DATE:
JYC	4/7/2010

DRAWING TITLE:			
Stainless Steel (304) Cable Ties			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-1225	TA-1225.dwg	A
SCALE:	NTS	U.O.M.: mm [INCHES]	SHEET: 1 OF 1