



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1172	A	RELEASED	HYO	5/8/01	JC	5/9/01	DJC	5/11/01
1884	B	Update To RoHS Compliant	EO	1/25/06	HO	1/25/06	HO	1/25/06



SPC Type No.	Spool Length (Feet)	Width (Inches)	Spool Color
1621	5	0.025	Silver
1623		0.050	Gold
1625		0.075	Green
1627		0.100	Blue
1629		0.125	Brown
1622	10	0.025	Silver
1624		0.050	Gold
1626		0.075	Green
1628		0.100	Blue
3326		0.125	Brown



SPECIFICATIONS:

1. Rosin: Pure type 'R' that meets all requirements of MIL-F-14256F type 'R'.
2. Spool: Static dissipative spool that meets all the requirements of MIL Standard 2000 and compliance with DOD Standard 1686A.
3. Cleaned and manufactured utilizing the latest technology in environmental friendly chemicals and processes.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
HISHAM ODISH	5/8/01
CHECKED BY:	DATE:
JOHN COLE	5/9/01
APPROVED BY:	DATE:
DANIEL CAREY	5/11/01

DRAWING TITLE: RoHS COMPLIANT ANTI - STATIC DESOLDERING BRAID			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-330	TA-330.DWG	B
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	