


REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	A	RELEASED	EO	03/21/06	TL	05/15/06	HO	05/15/06
1921	B	Title was "Female"	JWM	10/11/06	TUL	10/11/06	TUL	10/11/06



RoHS Compliant



SPECIFICATION:

- Shell: Steel, Nickel-Plated
- Contact: Brass, Gold-Plated
- Insulator: PBT & Glass-Fibre Reinforced, UL94V-0, Blue Color
- Current Rating: 5 Amp
- Dielectric Strength: 1000V for One Minute
- Insulator Resistance: 1000MΩ Min. @ 500 VDC
- Temperature: -55°C to +105°C

SPC Type No.	No of Pins	A	B	C	D	E	F	G	H
SPC15257	14P	12.96 [0.510]	25.60 [1.007]	38.10 [1.500]	29.00 [1.142]	7.60 [0.299]	21.60 [0.850]	39.70 [1.563]	7.0 [0.275]
SPC15336	24P	23.76 [0.935]	36.30 [1.429]	48.80 [1.921]	39.90 [1.570]	8.20 [0.323]	21.20 [0.835]	40.20 [1.583]	9.0 [0.354]
SPC15366	50P	51.84 [2.040]	64.40 [2.535]	77.00 [3.031]	68.20 [2.685]	8.50 [0.335]	24.90 [0.980]	43.60 [1.717]	12.5 [0.492]

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
Unless Otherwise Specified
.X ±0.2 [0.008]
.XX ±0.12 [0.005]

DRAWN BY: EKLAS ODISH
DATE: 03/21/06
CHECKED BY: THOMAS LEE
DATE: 05/15/06
APPROVED BY: HISHAM ODISH
DATE: 05/15/06

DRAWING TITLE: CENTRONIC MALE CONNECTOR, WITH METAL HOOD, RoHS

SIZE: A	DWG. NO.: TA-701	ELECTRONIC FILE: TA-701.DWG	REV: B
SCALE: NTS	U.O.M.: mm [INCHES]	SHEET: 1 OF 1	