

COPPER CABLES (UTP)

CAT6 550-MHz Patch Cables with Snagless Boots

	Gray	Blue	Green	Red	Yellow	Beige	Pink	Black	Purple	Orange	White
1-ft	EVNSL640-0001	EVNSL641-0001	EVNSL642-0001	EVNSL643-0001	EVNSL644-0001	EVNSL645-0001	EVNSL646-0001	EVNSL647-0001	EVNSL648-0001	EVNSL649-0001	EVNSL650-0001
2-ft	EVNSL640-0002	EVNSL641-0002	EVNSL642-0002	EVNSL643-0002	EVNSL644-0002	EVNSL645-0002	EVNSL646-0002	EVNSL647-0002	EVNSL648-0002	EVNSL649-0002	EVNSL650-0002
3-ft	EVNSL640-0003	EVNSL641-0003	EVNSL642-0003	EVNSL643-0003	EVNSL644-0003	EVNSL645-0003	EVNSL646-0003	EVNSL647-0003	EVNSL648-0003	EVNSL649-0003	EVNSL650-0003
4-ft	EVNSL640-0004	EVNSL641-0004	EVNSL642-0004	EVNSL643-0004	EVNSL644-0004	EVNSL645-0004	EVNSL646-0004	EVNSL647-0004	EVNSL648-0004	EVNSL649-0004	EVNSL650-0004
5-ft	EVNSL640-0005	EVNSL641-0005	EVNSL642-0005	EVNSL643-0005	EVNSL644-0005	EVNSL645-0005	EVNSL646-0005	EVNSL647-0005	EVNSL648-0005	EVNSL649-0005	EVNSL650-0005
6-ft	EVNSL640-0006	EVNSL641-0006	EVNSL642-0006	EVNSL643-0006	EVNSL644-0006	EVNSL645-0006	EVNSL646-0006	EVNSL647-0006	EVNSL648-0006	EVNSL649-0006	EVNSL650-0006
7-ft	EVNSL640-0007	EVNSL641-0007	EVNSL642-0007	EVNSL643-0007	EVNSL644-0007	EVNSL645-0007	EVNSL646-0007	EVNSL647-0007	EVNSL648-0007	EVNSL649-0007	EVNSL650-0007
10-ft	EVNSL640-0010	EVNSL641-0010	EVNSL642-0010	EVNSL643-0010	EVNSL644-0010	EVNSL645-0010	EVNSL646-0010	EVNSL647-0010	EVNSL648-0010	EVNSL649-0010	EVNSL650-0010
15-ft	EVNSL640-0015	EVNSL641-0015	EVNSL642-0015	EVNSL643-0015	EVNSL644-0015	EVNSL645-0015	EVNSL646-0015	EVNSL647-0015	EVNSL648-0015	EVNSL649-0015	EVNSL650-0015
20-ft	EVNSL640-0020	EVNSL641-0020	EVNSL642-0020	EVNSL643-0020	EVNSL644-0020	EVNSL645-0020	EVNSL646-0020	EVNSL647-0020	EVNSL648-0020	EVNSL649-0020	EVNSL650-0020
25-ft	EVNSL640-0025	EVNSL641-0025	EVNSL642-0025	EVNSL643-0025	EVNSL644-0025	EVNSL645-0025	EVNSL646-0025	EVNSL647-0025	EVNSL648-0025	EVNSL649-0025	EVNSL650-0025
50-ft	EVNSL640-0050	EVNSL641-0050	EVNSL642-0050	EVNSL643-0050	EVNSL644-0050	EVNSL645-0050	EVNSL646-0050	EVNSL647-0050	EVNSL648-0050	EVNSL649-0050	EVNSL650-0050

Custom Lengths Available Upon Request

CAT6 550-MHz Patch Cables with Basic Connectors

	Gray	Blue	Green	Red	Yellow	Beige	Pink	Black	Purple	Orange	White
1-ft	EVNSL620-0001	EVNSL621-0001	EVNSL622-0001	EVNSL623-0001	EVNSL624-0001	EVNSL625-0001	EVNSL626-0001	EVNSL627-0001	EVNSL628-0001	EVNSL629-0001	EVNSL630-0001
2-ft	EVNSL620-0002	EVNSL621-0002	EVNSL622-0002	EVNSL623-0002	EVNSL624-0002	EVNSL625-0002	EVNSL626-0002	EVNSL627-0002	EVNSL628-0002	EVNSL629-0002	EVNSL630-0002
3-ft	EVNSL620-0003	EVNSL621-0003	EVNSL622-0003	EVNSL623-0003	EVNSL624-0003	EVNSL625-0003	EVNSL626-0003	EVNSL627-0003	EVNSL628-0003	EVNSL629-0003	EVNSL630-0003
4-ft	EVNSL620-0004	EVNSL621-0004	EVNSL622-0004	EVNSL623-0004	EVNSL624-0004	EVNSL625-0004	EVNSL626-0004	EVNSL627-0004	EVNSL628-0004	EVNSL629-0004	EVNSL630-0004
5-ft	EVNSL620-0005	EVNSL621-0005	EVNSL622-0005	EVNSL623-0005	EVNSL624-0005	EVNSL625-0005	EVNSL626-0005	EVNSL627-0005	EVNSL628-0005	EVNSL629-0005	EVNSL630-0005
6-ft	EVNSL620-0006	EVNSL621-0006	EVNSL622-0006	EVNSL623-0006	EVNSL624-0006	EVNSL625-0006	EVNSL626-0006	EVNSL627-0006	EVNSL628-0006	EVNSL629-0006	EVNSL630-0006
7-ft	EVNSL620-0007	EVNSL621-0007	EVNSL622-0007	EVNSL623-0007	EVNSL624-0007	EVNSL625-0007	EVNSL626-0007	EVNSL627-0007	EVNSL628-0007	EVNSL629-0007	EVNSL630-0007
10-ft	EVNSL620-0010	EVNSL621-0010	EVNSL622-0010	EVNSL623-0010	EVNSL624-0010	EVNSL625-0010	EVNSL626-0010	EVNSL627-0010	EVNSL628-0010	EVNSL629-0010	EVNSL630-0010
15-ft	EVNSL620-0015	EVNSL621-0015	EVNSL622-0015	EVNSL623-0015	EVNSL624-0015	EVNSL625-0015	EVNSL626-0015	EVNSL627-0015	EVNSL628-0015	EVNSL629-0015	EVNSL630-0015
20-ft	EVNSL620-0020	EVNSL621-0020	EVNSL622-0020	EVNSL623-0020	EVNSL624-0020	EVNSL625-0020	EVNSL626-0020	EVNSL627-0020	EVNSL628-0020	EVNSL629-0020	EVNSL630-0020
25-ft	EVNSL620-0025	EVNSL621-0025	EVNSL622-0025	EVNSL623-0025	EVNSL624-0025	EVNSL625-0025	EVNSL626-0025	EVNSL627-0025	EVNSL628-0025	EVNSL629-0025	EVNSL630-0025
50-ft	EVNSL620-0050	EVNSL621-0050	EVNSL622-0050	EVNSL623-0050	EVNSL624-0050	EVNSL625-0050	EVNSL626-0050	EVNSL627-0050	EVNSL628-0050	EVNSL629-0050	EVNSL630-0050

What makes Black Box patch cables better than the competition?

Our patch cords use only high-quality components and EIA/TIA compliant enhanced connectors. These cables undergo rigorous testing to verify that they meet or exceed EIA/TIA performance standards. Black Box patch cables are available in many lengths, colors, and configurations, and are usually in stock and ready to ship. [Black Box also offers later shipping cut-off times for over-night and 2nd day orders than our competitors.](#)

For more information, please contact Black Box's **FREE** 24x7x365 Technical Support Dept. by dialing: 877-ASK BBOX or 877-877-2269



COPPER CABLES (UTP)

CAT5e 100-MHz Patch Cables with Molded Boots

	Blue	Green	Red	Yellow	Beige	Pink	Black	Purple	Orange
1-ft	EVNSL21E-0001	EVNSL22E-0001	EVNSL23E-0001	EVNSL24E-0001	EVNSL25E-0001	EVNSL26E-0001	EVNSL27E-0001	EVNSL28E-0001	EVNSL29E-0001
3-ft	EVNSL21E-0003	EVNSL22E-0003	EVNSL23E-0003	EVNSL24E-0003	EVNSL25E-0003	EVNSL26E-0003	EVNSL27E-0003	EVNSL28E-0003	EVNSL29E-0003
6-ft	EVNSL21E-0006	EVNSL22E-0006	EVNSL23E-0006	EVNSL24E-0006	EVNSL25E-0006	EVNSL26E-0006	EVNSL27E-0006	EVNSL28E-0006	EVNSL29E-0006
10-ft	EVNSL21E-0010	EVNSL22E-0010	EVNSL23E-0010	EVNSL24E-0010	EVNSL25E-0010	EVNSL26E-0010	EVNSL27E-0010	EVNSL28E-0010	EVNSL29E-0010
15-ft	EVNSL21E-0015	EVNSL22E-0015	EVNSL23E-0015	EVNSL24E-0015	EVNSL25E-0015	EVNSL26E-0015	EVNSL27E-0015	EVNSL28E-0015	EVNSL29E-0015
20-ft	EVNSL21E-0020	EVNSL22E-0020	EVNSL23E-0020	EVNSL24E-0020	EVNSL25E-0020	EVNSL26E-0020	EVNSL27E-0020	EVNSL28E-0020	EVNSL29E-0020
25-ft	EVNSL21E-0025	EVNSL22E-0025	EVNSL23E-0025	EVNSL24E-0025	EVNSL25E-0025	EVNSL26E-0025	EVNSL27E-0025	EVNSL28E-0025	EVNSL29E-0025
30-ft	EVNSL21E-0030	EVNSL22E-0030	EVNSL23E-0030	EVNSL24E-0030	EVNSL25E-0030	EVNSL26E-0030	EVNSL27E-0030	EVNSL28E-0030	EVNSL29E-0030
50-ft	EVNSL21E-0050	EVNSL22E-0050	EVNSL23E-0050	EVNSL24E-0050	EVNSL25E-0050	EVNSL26E-0050	EVNSL27E-0050	EVNSL28E-0050	EVNSL29E-0050

Custom Lengths Available Upon Request

CAT5e 100-MHz Patch Cable with Basic Connectors

	Blue	Green	Red	Yellow	Beige	Pink	Black	White	Gray	Purple	Orange
1-ft	EVNSL01E-0001	EVNSL02E-0001	EVNSL03E-0001	EVNSL04E-0001	EVNSL05E-0001	EVNSL06E-0001	EVNSL07E-0001	EVNSL10E-0001	EVNSL11E-0001	EVNSL13E-0001	EVNSL14E-0001
2-ft	EVNSL01E-0002	EVNSL02E-0002	EVNSL03E-0002	EVNSL04E-0002	EVNSL05E-0002	EVNSL06E-0002	EVNSL07E-0002	EVNSL10E-0002	EVNSL11E-0002	EVNSL13E-0002	EVNSL14E-0002
3-ft	EVNSL01E-0003	EVNSL02E-0003	EVNSL03E-0003	EVNSL04E-0003	EVNSL05E-0003	EVNSL06E-0003	EVNSL07E-0003	EVNSL10E-0003	EVNSL11E-0003	EVNSL13E-0003	EVNSL14E-0003
4-ft	EVNSL01E-0004	EVNSL02E-0004	EVNSL03E-0004	EVNSL04E-0004	EVNSL05E-0004	EVNSL06E-0004	EVNSL07E-0004	EVNSL10E-0004	EVNSL11E-0004	EVNSL13E-0004	EVNSL14E-0004
5-ft	EVNSL01E-0005	EVNSL02E-0005	EVNSL03E-0005	EVNSL04E-0005	EVNSL05E-0005	EVNSL06E-0005	EVNSL07E-0005	EVNSL10E-0005	EVNSL11E-0005	EVNSL13E-0005	EVNSL14E-0005
6-ft	EVNSL01E-0006	EVNSL02E-0006	EVNSL03E-0006	EVNSL04E-0006	EVNSL05E-0006	EVNSL06E-0006	EVNSL07E-0006	EVNSL10E-0006	EVNSL11E-0006	EVNSL13E-0006	EVNSL14E-0006
7-ft	EVNSL01E-0007	EVNSL02E-0007	EVNSL03E-0007	EVNSL04E-0007	EVNSL05E-0007	EVNSL06E-0007	EVNSL07E-0007	EVNSL10E-0007	EVNSL11E-0007	EVNSL13E-0007	EVNSL14E-0007
10-ft	EVNSL01E-0010	EVNSL02E-0010	EVNSL03E-0010	EVNSL04E-0010	EVNSL05E-0010	EVNSL06E-0010	EVNSL07E-0010	EVNSL10E-0010	EVNSL11E-0010	EVNSL13E-0010	EVNSL14E-0010
15-ft	EVNSL01E-0015	EVNSL02E-0015	EVNSL03E-0015	EVNSL04E-0015	EVNSL05E-0015	EVNSL06E-0015	EVNSL07E-0015	EVNSL10E-0015	EVNSL11E-0015	EVNSL13E-0015	EVNSL14E-0015
20-ft	EVNSL01E-0020	EVNSL02E-0020	EVNSL03E-0020	EVNSL04E-0020	EVNSL05E-0020	EVNSL06E-0020	EVNSL07E-0020	EVNSL10E-0020	EVNSL11E-0020	EVNSL13E-0020	EVNSL14E-0020
25-ft	EVNSL01E-0025	EVNSL02E-0025	EVNSL03E-0025	EVNSL04E-0025	EVNSL05E-0025	EVNSL06E-0025	EVNSL07E-0025	EVNSL10E-0025	EVNSL11E-0025	EVNSL13E-0025	EVNSL14E-0025
50-ft	EVNSL01E-0050	EVNSL02E-0050	EVNSL03E-0050	EVNSL04E-0050	EVNSL05E-0050	EVNSL06E-0050	EVNSL07E-0050	EVNSL10E-0050	EVNSL11E-0050	EVNSL13E-0050	EVNSL14E-0050

Custom Lengths Available Upon Request

This is a Patch Cable with a BASIC Connector -->



This is a Patch Cable with a MOLDED BOOT -->

