

Product Selection Guide

Product	Features					Cleaning Ability			Cleaning Methods					
	Plastic Safe	Nonflammable	No Ozone Depleting Chemicals	Dries Fast	Dielectric Breakdown (Aerosol)	Grease	Oil	Ionic Soils	Aerosol Spray	Vapor Degreasing	Ultrasonics		Hot Immersion	Cold Immersion
Cleaner Degreasers														
Electro-Wash® Tri-V		✓	✓	✓	8kV	1	1	2	✓	✓	✓		✓	Strongest Cleaner
Electro-Wash® Delta		✓	✓	✓	31kV	2	1	2	✓		✓		✓	
Electro-Wash® NX0		✓	✓	✓	15kV	1	1	2	✓	✓	✓		✓	
Electro-Wash® QD	✓	✓	✓	✓	11kV	3	1	2	✓					
Electro-Wash® VZ		✓	✓	✓	17kV	3	1	2	✓	✓	✓		✓	
Electro-Wash® PX	✓		✓	✓		1	1	1	✓				✓	
Electro-Wash® MX	✓		✓			1	1	1	✓					
Electro-Wash® PR	✓		✓	✓		1	1	-	✓					
Electro-Wash® CZ	✓	✓	✓	✓	17kV	3	2	2	✓	✓	✓		✓	
Electro-Wash® Two Step		✓	✓			1	1	1			✓	✓	✓	Most Plastic-Safe

Industrial Degreasers

Max-Kleen® Tri-V		✓	✓	✓	8kV	1	1	2	✓	✓	✓		✓
Max-Kleen™ Citrus		✓	✓		62kV	2	2	2	✓		✓	✓	✓
Max-Kleen™ Citrus HF			✓		62kV	1	1	3			✓	✓	✓

1-Excellent 2-Good 3-Fair R-Regular Strength X-Extra Strength