


**The New EZCODE Label Printer
Redefines Easy to Use!**



EZCODE[®]

EZL500 Thermal
Label Printer



EZL500 Thermal Label Printer

The industry's most sophisticated label printer is also the easiest to use. It's so smart, it's simple!

- Large LCD screen makes viewing easy
- Powerful firmware is easy to use and update
- Ergonomic design makes it easy to carry
- Thermal transfer technology enables you to print non-smearing labels
- Cut a label with just the touch of a button
- Large tape cassette maximizes the amount of tape media
- Wide output port makes it easy to collect your printed labels
- Backlit display enables use in low-light environments
- Oversized keys and spacing make it easy to type labels
- Integral cassette sensor automatically adjusts the unit to your tape's width and media type, eliminating reprogramming with each tape switch
- Can be outfitted with a long-life, rechargeable, 7.4-volt Li-ion battery



With the EZCODE® EZL500 thermal label printer, you can print the widest variety of labels used on the most surface types — and you can use it in more work environments than any other thermal label printer on the market. Best of all, it's easier to use than any other thermal label printer. With the EZL500 printer, you'll be labeling cable jackets and other surfaces in no time at all!

It's easy to get a handle on things

The printer's simple-to-use but powerful firmware makes operation intuitive, so you won't spend valuable time reading the instruction manual. The ergonomically designed EZL500 printer fits comfortably in your hand. Rubber molding enables a firm grip and helps to protect the unit in case of an accidental drop. The EZL500 printer features the largest backlit LCD screen among all handheld thermal label printers. It enables you to easily see information on display and is especially useful in low-light conditions.

Just print, cut and stick

Using thermal transfer technology, the EZL500 unit prints labels that won't smear. Based on average usage, the print head can be expected to last up to 10 years. Now that's reliability! The automatic cutter function enables you to cut a label with the touch of a button. And unlike some competing models, the cutting blade can be changed easily.

Size matters

You'll appreciate the EZL500 printer's oversized, wide-spaced keys, so you won't hit multiple buttons by mistake. Use hard-coded function keys for immediate access to frequently used functions. Soft-menu keys are ideal for infrequent functions. Able to handle a variety of tapes ranging from a quarter-inch to an inch wide, the EZL500 printer enables you to use more media than any other thermal label printer. The integral cassette sensor automatically adjusts the unit to your tape's width and media type — so you don't have to reprogram the printer with each cassette change!




Do more, do more longer

The EZL500 printer runs on six standard AA batteries or an optional, rechargeable 7.4-volt Li-ion battery. The Li-ion battery has a longer life than standard batteries and lasts longer than most other rechargeable batteries.

In short, the EZL500 printer is ready to work on the lengthy jobs you have now and the ones you'll be doing years down the road.



When you're working in tight spaces, the handy magnet strap lets you to stick the EZL500 printer to a vertical metallic surface to free your hands until you need to use it again.



With the included PC connection software and built-in mini USB port, you can print directly from your computer and easily upgrade the software

EZL500 Thermal Label Printer



EZL500 Thermal Label Printer

Cat. Number	Description	UPC Number
EZL500	Handheld Thermal Label Printer (includes EZL500 Thermal Label Printer, EZ-1030C-WN label cassette, six AA batteries, quick-start guide and user's manual)	782609-91656
EZL500-KIT	Handheld Thermal Label Printer Kit with Accessories (includes EZL500 Thermal Label Printer, EZ-1030C-MP and EZ-1030C-WN label cassettes, PA-EZL500 power adapter, MS-EZL500 magnet strap, PCS-EZL500 PC software and USB cable, RB-EZL500 rechargeable battery, quick-start guide, user's manual and CC-EZL500 carrying case)	782609-91657



EZL500 Accessories

Cat. Number	Description	UPC Number
PA-EZL500	EZL500 Power Adapter	786209-91682
MS-EZL500	Magnet Strap for EZL500	786209-91683
PCS-EZL500	PC Software and USB Cable for EZL500	786209-91685
CC-EZL500	Hard Carrying Case for EZL500	786209-91686
RB-EZL500	EZL500 Rechargeable Battery	786209-92262

EZL500 Thermal Label Printer Tapes

- **Nylon** — Excellent for wire and cable wrapping on curved, textured and highly textured surfaces, these flexible labels feature EZ-Peel split backs and industrial-strength adhesive
- **Polyester** — Perfect for general labeling on flat or textured surfaces, these labels also come with EZ-Peel split backs and industrial-strength adhesive
- **Heat-Shrink** — Made of flame-retardant polyolefin with 3:1 shrink ratio for extra protection and insulation of wire and cable, these labels meet MIL-DTL-23053/5 classes 1 and 3 standards
- **Vinyl** — Able to resist oil, dirt, grime and solvents on smooth, textured or curved surfaces, this flexible label features an EZ-Peel split back and industrial-strength adhesive; it's excellent for indoor/outdoor use



EZ-1230C-WN



EZ-3430C-WP

EZL500 Label Printer Tapes

Cat. Number	Material	Color	Width	UPC Number
EZ-3830C-WN	Nylon	White	3/8"	786209-91658
EZ-1230C-WN	Nylon	White	1/2"	786209-91659
EZ-3430C-WN	Nylon	White	3/4"	786209-91660
EZ-1030C-WN	Nylon	White	1"	786209-91661
EZ-3830C-YN	Nylon	Yellow	3/8"	786209-91662
EZ-1230C-YN	Nylon	Yellow	1/2"	786209-91663
EZ-3430C-YN	Nylon	Yellow	3/4"	786209-91664
EZ-1030C-YN	Nylon	Yellow	1"	786209-91665
EZ-3830C-WP	Polyester	White	3/8"	786209-91666
EZ-1230C-WP	Polyester	White	1/2"	786209-91667
EZ-3430C-WP	Polyester	White	3/4"	786209-91668
EZ-1030C-WP	Polyester	White	1"	786209-91670
EZ-3830C-MP	Polyester	Metallic	3/8"	786209-91671
EZ-1230C-MP	Polyester	Metallic	1/2"	786209-91672
EZ-3430C-MP	Polyester	Metallic	3/4"	786209-91673
EZ-1030C-MP	Polyester	Metallic	1"	786209-91674
EZ-1412C-WHS	Heat-Shrink	White	1/4"	786209-91675
EZ-3812C-WHS	Heat-Shrink	White	3/8"	786209-91676
EZ-1212C-WHS	Heat-Shrink	White	1/2"	786209-91677
EZ-1412C-YHS	Heat-Shrink	Yellow	1/4"	786209-91678
EZ-3812C-YHS	Heat-Shrink	Yellow	3/8"	786209-91679
EZ-1212C-YHS	Heat-Shrink	Yellow	1/2"	786209-91680
EZ-1030C-SL	Self-Laminating Vinyl	White/Clear	1"	786209-91681

www.tnb.com

Thomas & Betts

Please ask your Thomas & Betts sales representative for a complete catalog of quality Thomas & Betts electrical products or visit us at www.tnb.com. For customer service, call 1-800-816-7809. For technical questions, call 1-888-862-3289.

Thomas & Betts Corporation
Electrical Division
8155 T&B Boulevard
Memphis, TN 38125
901-252-5000

Thomas & Betts Ltd.
700 Thomas Avenue
Iberville, Québec J2X 2M9
450-347-5318