


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	RELEASED	M.O.				D.D.	7/27/84
1090	B	CHG. FILE NAME, WAS ON K-XXX.DG	HYO	10/10/01	JC	10/16/01	JC	10/16/01

SPC Type No.	No. Of Column	No. Of Rows	No. Of Compartments	Compartment Size (Inches)		Overall Box Size (Inches)					
				Length	Width	Outer Length	Outer Width	Outer Height	Inner Length	Inner Width	Inner Height
K-606	6	Zero	6	1 5/8	6 9/16	11	6 3/4	1 3/4	10 1/2	6 9/16	1 1/2
K-602	6	2	12	1 5/8	3	11	6 3/4	1 3/4	10 1/2	6 9/16	1 1/2
K-618	6	3	18	1 3/4	1 3/4	11	6 3/4	1 3/4	10 1/2	6 9/16	1 1/2
K-806	6	Zero	6	2	8 3/8	13 1/8	9	2 5/16	12 1/2	8 3/8	2 1/16
K-812	6	2	12	2	4 1/8	13 1/8	9	2 5/16	12 5/8	8 3/8	2
K-824	6	4	24	2	2	13 1/8	9	2 5/16	12 5/8	8 3/8	2
K-203	6	Zero	6	1 1/4	4	8 1/4	4 1/2	1 3/8	8	4	1 1/8
K-208	6	2	12	1 1/4	2	8 1/4	4 1/2	1 3/8	8	4	1 1/8
K-200	6	3	18	1 1/4	1 1/4	8 1/4	4 1/2	1 3/8	8	4	1 1/8
K-166	6	6	36	1 1/2	1	10	7 1/8	1 11/16	9 3/4	6 7/8	1 1/2

SPECIFICATIONS:

1. Material: High - Impact transparent k-Resin
2. comes with hinged lid



SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	M.O.		UTILITY BOXES			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	APPROVED BY:	DATE:	A	TA-425	TA-425.DWG	B
D.D.	7/27/84	SCALE: NTS	U.O.M.: INCHES	SHEET: 1 OF 1		