


this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Divya	20-11-08	Suresh	20-11-08	JN	12/12/08



STRAIN RELIEF SHOWN AS ILLUSTRATION ONLY

ITEM	DESCRIPTION	MATERIAL	FINISH
5	CABLE	-	-
4	TUBING	**HEAT SHRINK	BLACK
3	STRAIN RELIEF	POLYVINYL CHLORIDE	BLACK
2	UHF MALE CRIMP	BRASS	NICKEL
1	BNC MALE CRIMP	BRASS	NICKEL

\*\*DUAL WALL POLYOLEFIN

Manufacturer Part Number	Product Description	Length	Cable Type	Strain Relief
SPC20832	BNC MALE TO UHF MALE; RG-58A/U; 12"; CR/CR	12	RG-58A/U	Yes
SPC27124	BNC MALE TO UHF MALE; RG-58A/U; 24"; CR/CR	24	RG-58A/U	Yes
SPC27126	BNC MALE TO UHF MALE; RG-58A/U; 36"; CR/CR	36	RG-58A/U	Yes
SPC27128	BNC MALE TO UHF MALE; RG-58A/U; 48"; CR/CR	48	RG-58A/U	Yes
SPC27130	BNC MALE TO UHF MALE; RG-58A/U; 60"; CR/CR	60	RG-58A/U	Yes
SPC20833	BNC MALE TO UHF MALE; RG-58A/U; 72"; CR/CR	72	RG-58A/U	Yes
SPC27133	BNC MALE TO UHF MALE; RG-58C/U; 12"; CR/CR	12	RG-58C/U	Yes
SPC27134	BNC MALE TO UHF MALE; RG-58C/U; 24"; CR/CR	24	RG-58C/U	Yes
SPC27135	BNC MALE TO UHF MALE; RG-58C/U; 36"; CR/CR	36	RG-58C/U	Yes
SPC27136	BNC MALE TO UHF MALE; RG-58C/U; 48"; CR/CR	48	RG-58C/U	Yes
SPC27137	BNC MALE TO UHF MALE; RG-58C/U; 60"; CR/CR	60	RG-58C/U	Yes
SPC27138	BNC MALE TO UHF MALE; RG-58C/U; 72"; CR/CR	72	RG-58C/U	Yes
SPC27139	BNC MALE TO UHF MALE; RG-55B/U; 12"; CR/CR	12	RG-55B/U	No
SPC27140	BNC MALE TO UHF MALE; RG-55B/U; 24"; CR/CR	24	RG-55B/U	No
SPC27141	BNC MALE TO UHF MALE; RG-55B/U; 36"; CR/CR	36	RG-55B/U	No
SPC27142	BNC MALE TO UHF MALE; RG-55B/U; 48"; CR/CR	48	RG-55B/U	No
SPC27143	BNC MALE TO UHF MALE; RG-55B/U; 60"; CR/CR	60	RG-55B/U	No
SPC27144	BNC MALE TO UHF MALE; RG-55B/U; 72"; CR/CR	72	RG-55B/U	No
SPC27145	BNC MALE TO UHF MALE; RG-223/U; 12"; CR/CR	12	RG-223/U	No
SPC27146	BNC MALE TO UHF MALE; RG-223/U; 24"; CR/CR	24	RG-223/U	No
SPC27147	BNC MALE TO UHF MALE; RG-223/U; 36"; CR/CR	36	RG-223/U	No
SPC27148	BNC MALE TO UHF MALE; RG-223/U; 48"; CR/CR	48	RG-223/U	No
SPC27149	BNC MALE TO UHF MALE; RG-223/U; 60"; CR/CR	60	RG-223/U	No
SPC27150	BNC MALE TO UHF MALE; RG-223/U; 72"; CR/CR	72	RG-223/U	No
SPC27151	BNC MALE TO UHF MALE; RG-142B/U; 12"; CR/CR	12	RG-142B/U	No

**Disclaimer:**  
All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



**SPC TECHNOLOGY**

Drawing Title: **BNC MALE CRIMP TO UHF MALE CRIMP**

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By:	Date:
Divya	20-11-08
Checked By:	Date:
Suresh	20-11-08
Approved By:	Date:
Jason Nash	12/12/08

Size: A	Dwg. No TA-983	Electronic File TA-983.dwg	Rev A
---------	----------------	----------------------------	-------

Scale: NTS U.O.M.: Inches (mm) Sheet: 1 of 2

All rights Reserved . No Portion of this publication, whether in whole or in part can be reproduced without the express written consent of SPC Technology.

Revisions:			DOC. No.		* Effective: 12/21/98		* DCP No. 680	
DCP: #	REV	Description:	Drawn	Date	Checked	Date	Approved	Date
XXX	A	RELEASED	Divya	20-11-08	Suresh	20-11-08	JN	12/12/08



Manufacturer Part Number	Product Description	Length	Cable Type	Strain Relief
SPC27152	BNC MALE TO UHF MALE; RG-142B/U; 24"; CR/CR	24	RG-142B/U	No
SPC27153	BNC MALE TO UHF MALE; RG-142B/U; 36"; CR/CR	36	RG-142B/U	No
SPC27154	BNC MALE TO UHF MALE; RG-142B/U; 48"; CR/CR	48	RG-142B/U	No
SPC27155	BNC MALE TO UHF MALE; RG-142B/U; 60"; CR/CR	60	RG-142B/U	No
SPC27156	BNC MALE TO UHF MALE; RG-142B/U; 72"; CR/CR	72	RG-142B/U	No
SPC27157	BNC MALE TO UHF MALE; RG-400/U; 12"; CR/CR	12	RG-400/U	No
SPC27158	BNC MALE TO UHF MALE; RG-400/U; 24"; CR/CR	24	RG-400/U	No
SPC27159	BNC MALE TO UHF MALE; RG-400/U; 36"; CR/CR	36	RG-400/U	No
SPC27160	BNC MALE TO UHF MALE; RG-400/U; 48"; CR/CR	48	RG-400/U	No
SPC27161	BNC MALE TO UHF MALE; RG-400/U; 60"; CR/CR	60	RG-400/U	No
SPC27162	BNC MALE TO UHF MALE; RG-400/U; 72"; CR/CR	72	RG-400/U	No
SPC27163	BNC MALE TO UHF MALE; LMR-195; 12"; CR/CR	12	LMR-195	No
SPC27164	BNC MALE TO UHF MALE; LMR-195; 24"; CR/CR	24	LMR-195	No
SPC27165	BNC MALE TO UHF MALE; LMR-195; 36"; CR/CR	36	LMR-195	No
SPC27166	BNC MALE TO UHF MALE; LMR-195; 48"; CR/CR	48	LMR-195	No
SPC27167	BNC MALE TO UHF MALE; LMR-195; 60"; CR/CR	60	LMR-195	No
SPC27168	BNC MALE TO UHF MALE; LMR-195; 72"; CR/CR	72	LMR-195	No
SPC27169	BNC MALE TO UHF MALE; RG-59B/U; 12"; CR/CR	12	RG-59B/U	No
SPC27170	BNC MALE TO UHF MALE; RG-59B/U; 24"; CR/CR	24	RG-59B/U	No
SPC27171	BNC MALE TO UHF MALE; RG-59B/U; 36"; CR/CR	36	RG-59B/U	No
SPC27172	BNC MALE TO UHF MALE; RG-59B/U; 48"; CR/CR	48	RG-59B/U	No
SPC27173	BNC MALE TO UHF MALE; RG-59B/U; 60"; CR/CR	60	RG-59B/U	No
SPC27174	BNC MALE TO UHF MALE; RG-59B/U; 72"; CR/CR	72	RG-59B/U	No
SPC27175	BNC MALE TO UHF MALE; RG-62A/U; 12"; CR/CR	12	RG-62A/U	No
SPC27176	BNC MALE TO UHF MALE; RG-62A/U; 24"; CR/CR	24	RG-62A/U	No
SPC27177	BNC MALE TO UHF MALE; RG-62A/U; 36"; CR/CR	36	RG-62A/U	No
SPC27178	BNC MALE TO UHF MALE; RG-62A/U; 48"; CR/CR	48	RG-62A/U	No
SPC27179	BNC MALE TO UHF MALE; RG-62A/U; 60"; CR/CR	60	RG-62A/U	No
SPC27180	BNC MALE TO UHF MALE; RG-62A/U; 72"; CR/CR	72	RG-62A/U	No
SPC27205	BNC MALE TO UHF MALE; RG-8/X; 12"; CR/CR	12	RG-8/X	No
SPC27206	BNC MALE TO UHF MALE; RG-8/X; 24"; CR/CR	24	RG-8/X	No
SPC27207	BNC MALE TO UHF MALE; RG-8/X; 36"; CR/CR	36	RG-8/X	No
SPC27208	BNC MALE TO UHF MALE; RG-8/X; 48"; CR/CR	48	RG-8/X	No
SPC27209	BNC MALE TO UHF MALE; RG-8/X; 60"; CR/CR	60	RG-8/X	No
SPC27210	BNC MALE TO UHF MALE; RG-8/X; 72"; CR/CR	72	RG-8/X	No
SPC27211	BNC MALE TO UHF MALE; LMR-240; 12"; CR/CR	12	LMR-240	No
SPC27212	BNC MALE TO UHF MALE; LMR-240; 24"; CR/CR	24	LMR-240	No
SPC27213	BNC MALE TO UHF MALE; LMR-240; 36"; CR/CR	36	LMR-240	No
SPC27214	BNC MALE TO UHF MALE; LMR-240; 48"; CR/CR	48	LMR-240	No
SPC27215	BNC MALE TO UHF MALE; LMR-240; 60"; CR/CR	60	LMR-240	No
SPC27216	BNC MALE TO UHF MALE; LMR-240; 72"; CR/CR	72	LMR-240	No

**Disclaimer:**

All statements and technical information contained herein are based upon information and/or tests we believe to be accurate and reliable. Since conditions of use are beyond our control, the user shall determine the suitability of the product for the intended use and assume all risk and liability whatsoever in connection therewith.



**SPC TECHNOLOGY**

Drawing Title:

**BNC MALE CRIMP TO BNC FEMALE CRIMP BULKHEAD**

Unless otherwise specified, Dimensions are for references purposes only.

Drawn By:

Divya

Date:

20-11-08

Checked By:

Suresh

Date:

20-11-08

Approved By:

Jason Nash

Date:

12/12/08

Size:

A

Dwg. No

TA-983

Electronic File

TA-983.dwg

Rev

A

Scale: NTS

U.O.M.: Inches (mm)

Sheet: 2 of 2