

DATA SHEET

# DANTONA



DATA SHEET

Model No.. FH-7000

Specification

Nominal Voltage		1.2V	
Capacity (mAh)	Rate	0.2C	0.5C
	Nominal	7000	6300
	Typical	7050	7000
Approx Weight		190g	
Internal Resistance(at 1KHz)		≤10mΩ	
Charge	Standard	0.1C ×15hrs	
	Trickle	0.03C - 0.0625C	
Discharge cut-off voltage		1.0V	
Operation temp.	Standard charge	0 °C - 70 °C	
	Trickle charge	0 °C - 70 °C	
	Discharge	-20 °C - 70 °C	
Storage temperature		15 °C - 25 °C	
Relative humidity		65 ± 20%	

Dimension



(with tube)

NOTE:

1. Nominal capacity rated at 0.2C
2. Other capacity are for reference
3. Weight and internal resistance are for reference

Typical characteristics

