

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC-F005.DWG

REVISIONS				DOC. NO.	SPC-F005	* Effective:	7/8/02	* DCP No.	1398
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
2070	A	Released	JYC	3/2/2010	JYC	3/2/2010	JYC	3/2/2010	



Specification

1. Rated Voltage: 1.5VDC
2. Operating Voltage: 1~2VDC
3. Max. Rated Current: 30mA/1.5VDC
4. Min. Sound Pressure Level: 75dB/10cm
5. Resonant Frequency: 2300±500HZ
6. Response Time: 50ms
7. Case Material/Color: PBT/Black
8. Operating Temperature: -20~+70°C
9. Store Temperature: -30~+80°C
10. Weight: 2g



DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
Jerrald Chen	3/2/2010	Magnetic Buzzer	A	MCKPX-G1201UB-K4064	25R0862.dwg	A
CHECKED BY:	DATE:	SCALE:	NTS	U.D.M:	mm	SHEET:
Jerrald Chen	3/2/2010					1 OF 1
APPROVED BY:	DATE:					
Jerrald Chen	3/2/2010					