

SKM 75GB173D



SEMITRANS™ 2

IGBT Modules


SKM 75GB173D

Features

- N channel, Homogeneous Si
- Low inductance case
- Very low tail current with low temperature dependence
- High short circuit capability, self limiting to $6 \times I_{Cnom}$
- Latch-up free
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DCB Direct Copper Bonding
- Large clearance (10 mm) and creepage distance (20 mm)

Typical Applications







- AC inverter drives on mains 575 - 750 V_{AC}
- DC bus voltage 750 - 1200 V_{DC}
- Public transport (auxiliary syst.)
- Switching (not for linear use)












GB

Absolute Maximum Ratings		$T_c = 25\text{ °C}$, unless otherwise specified	
Symbol	Conditions	Values	Units
IGBT			
V_{CES}		1700	V
I_C	$T_c = 25\text{ (80) °C}$	75 (50)	A
I_{CRM}	$t_p = 1\text{ ms}$	100	A
V_{GES}		± 20	V
T_{vj} (T_{stg})	$T_{OPERATION} \leq T_{stg}$	- 40 ... + 150 (1 25)	°C
V_{isol}	AC, 1 min.	4000	V
Inverse diode			
I_F	$T_c = 25\text{ (80) °C}$	60 (40)	A
I_{FRM}	$t_p = 1\text{ ms}$	100	A
I_{FSM}	$t_p = 10\text{ ms}$; sin.; $T_j = 150\text{ °C}$	550	A

Characteristics		$T_c = 25\text{ °C}$, unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
IGBT					
$V_{GE(th)}$	$V_{GE} = V_{CE}$, $I_C = 4\text{ mA}$	4,8	5,5	6,2	V
I_{CES}	$V_{GE} = 0$, $V_{CE} = V_{CES}$, $T_j = 25\text{ (125) °C}$		0,1	0,3	mA
$V_{CE(TO)}$	$T_j = 25\text{ (125) °C}$		1,65 (1,9)	1,9 (2,15)	V
r_{CE}	$V_{GE} = 20\text{ V}$, $T_j = 25\text{ (125) °C}$		35 (46)	40 (57)	mΩ
$V_{CE(sat)}$	$I_{Cnom} = 50\text{ A}$, $V_{GE} = 15\text{ V}$, chip level		3,4 (4,2)	3,9 (5)	V
C_{ies}	under following conditions		8		nF
C_{oes}	$V_{GE} = 0$, $V_{CE} = 25\text{ V}$, $f = 1\text{ MHz}$		0,64		nF
C_{res}			0,25		nF
L_{CE}				30	nH
$R_{CC'+EE'}$	res., terminal-chip $T_c = 25\text{ (125) °C}$		0,75 (1)		mΩ
$t_{d(on)}$	$V_{CC} = 1200\text{ V}$, $I_{Cnom} = 50\text{ A}$		40		ns
t_r	$R_{Gon} = R_{Goff} = 12\text{ Ω}$, $T_j = 125\text{ °C}$		35		ns
$t_{d(off)}$	$V_{GE} = \pm 15\text{ V}$		400	600	ns
t_f			58		ns
$E_{on} (E_{off})$			18 (13)		mJ
Inverse diode					
$V_F = V_{EC}$	$I_{Fnom} = 50\text{ A}$; $V_{GE} = 0\text{ V}$; $T_j = 25\text{ (125) °C}$		2,2 (2)	2,7 (2,4)	V
$V_{(TO)}$	$T_j = 125\text{ () °C}$		1,3	1,5	V
r_T	$T_j = 125\text{ () °C}$		12	18	mΩ
I_{RRM}	$I_{Fnom} = 50\text{ A}$; $T_j = 25\text{ (125) °C}$		30 (43)		A
Q_{rr}	$di/dt = 800\text{ A/μs}$		7 (15)		μC
E_{rr}	$V_{GE} = V$				mJ
Thermal characteristics					
$R_{th(j-c)}$	per IGBT			0,25	K/W
$R_{th(j-c)D}$	per Inverse Diode			0,75	K/W
$R_{th(c-s)}$	per module			0,05	K/W
Mechanical data					
M_s	to heatsink M6	3		5	Nm
M_t	to terminals M5	2,5		5	Nm
w				160	g







This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.