




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			VEE	28-09-10	JAG	28-09-10	XXX	12-10-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398




Specifications:

1. Rated voltage : 3.6V
2. Operating voltage : 2.5 to 4.5V
3. Maximum rated current : 80mA
4. Coil resistance : 16 ±2.4W
5. Coil impedance : .40W
6. Minimum sound pressure level : 95dB/10cm
7. Resonant frequency : 300Hz.
8. Case material/color : LCP 6130/black
9. Operating temperature : -30 to +70°C
10. Store temperature : -40 to +85°C
11. Weight : 0.4g

Part Number Table

Description	Part Number
Magnetic Transducer	MCSMT-8540B-K4083



DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	VEE	DATE:	28-09-10
CHECKED BY:	JAG	DATE:	28-09-10
APPROVED BY:	XXX	DATE:	12-10-10

DRAWING TITLE:		Magnetic Transducer	
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	MCSMT-8540B-K4083	25R0977	A

SCALE:	NTS	U.O.M.:	Millimeters
SHEET:	1	OF	1