



SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.
SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			SHA	13-08-10	MRD	20-08-10	XXX	27-08-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398



Specifications:

Electrical :

Contact rating : 5A at 120 VAC or

28 VDC, 2A at 250 VAC

Contact resistance : 10 milliohms maximum

Insulation resistance : 1,000 megohms minimum at 500 VDC

Dielectric strength : 1,000 VRMS

Mechanical:

Life: 50,000 cycles

Environmental:

Operating Temperature: -30°C to +85°C

Material:

Case: DAP, UL 94V-0

Housing: Stainless Steel

Actuator: Nylon, Black

Bushing: Brass, Nickel Plated

Contact/Terminals: Copper Alloy, Silver Plated

Part Number Table

Description	Part Number
Rocker Switch, DPDT	SPC21144

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY: SHA

DATE: 13-08-10

DRAWING TITLE: Rocker Switch, DPDT

CHECKED BY: MRD

DATE: 20-08-10

SIZE DWG. NO. XXX

SCALE: NTS

U.O.M.: INCHES [mm]

ELECTRONIC FILE 53H6672

REV A

APPROVED BY: XXX

DATE: 27-08-10

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1

OF 1

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.