


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS		DOC. NO.	SPC-F005	Effective 12/21/08	DCP No	B90		
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1937	A	Released	JWM	2/22/00	JN	08/23/08	JN	08/23/08



SPECIFICATION

Electrical
 Contact Rating: 3 Amp @ 120 VAC or 28 VDC, 1 Amp @ 250 VAC
 Contact Resistance: 20 Milliohms max.
 Insulation Resistance: 1,000 Megohms Min. at 500VDC
 Dielectric Strength: 1,000 VRMS

Mechanical
 Life: 60,000 Cycles
 Environmental
 Operating Temperature: -30°C to +85°C

Materials
 Case: Diallyl Phthalate (DAP), UL 94V-0
 Actuator: Thermoplastic Polyester
 Bushing: Brass Nickel Plated
 Terminal Support: Brass, Tin plated
 Housing: Stainless Steel
 Contacts/Terminals: Copper Alloy, Contact Plating Silver
 Regulatory
 UL and Canada recognized component. UL/CUL

MODEL NO.	SWITCHING POSITION
SPC21193	OFF
CONN. TERMS	Open
SCHEMATIC	1-3

NOTES:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHEREASER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jeff McVicker	2/22/00
CHECKED BY:	DATE:
Jason Nash	09/23/08
APPROVED BY:	DATE:
Jason Nash	09/23/08



SPC TECHNOLOGY

DRAWING TITLE:
SUB-MINIATURE PUSHBUTTON SWITCH

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC21193	11M0387.dwg	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1