






SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISONS		DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
DCP #	REV		SID	03-08-10	JAG	05-08-10	XXX	17-08-10




Specifications:

Electrical:
 Contact rating : 5A at 120 VAC or 28 VDC , 2A at 250 VAC
 Contact resistance : 10 Milliohms maximum
 Insulation resistance : 1,000 Megohms minimum to 500 VDC
 Dielectric strength : 1,000 VRMS

Mechanical:
 Life : 30,000 Cycles

Environmental:
 Operating temperature : -30°C to +85°C

Material:
 Case : DAP, UL94V-0
 Housing : Stainless Steel
 Actuator : Nylon, Black
 Contacts/terminals : Copper Alloy, Gold Plated



Part Number Table

Description	Part Number
Slide Switch, SPDT, PCB Mount	SPC21128

Dimensions : Inches (mm)

Conn. Terms	Switching Function		
	ON	NONE	ON
2-1	Open	2-3	
Schematic	SPDT	<p>Non-Shorting Type</p>	

DISCLAIMER:
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE:	SCALE:	SHEET:
SID	03-08-10	Slide Switch, SPDT, PCB Mount	NTS	1 OF 1
CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE
JAG	05-08-10	XXX	XXX	53H6676
APPROVED BY:	DATE:	SCALE:	U.O.M.: INCHES [mm]	REV
XXX	17-08-10	NTS		A