SPC TECHNOLOGY


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
			ASH	02-08-10	JAG	14-08-10	XXX	16-08-10

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398






RoHS Compliant

Schematic

	Switching Position		
	Momentary	Off	Momentary
Connected Terminals	2-3	Open	2-1
	SPDT	2 Comm.	1 3

Solder Lug Terminals



Specifications:

Electrical
Contact rating: 5A at 120 VAC or
28 VDC, 2A at 250 VAC
Contact resistance: 10 milliohms maximum
Insulation resistance: 1,000 mega ohms minimum at 500 VDC
Dielectric strength: 1,000 VRMS

Mechanical
Life: 50,000 cycles

Environmental
Operating Temperature: -30°C to +85°C

Material
Case: DAP, UL 94V-0
Housing: Stainless Steel
Actuator: Nylon
Bushing: Brass, Nickel Plated
Support: Brass, Tin plated
Contact/Terminals: Copper Alloy, silver plated

Dimensions : Inches (mm)

Part Number Table

Description	Part Number
Rocker Switch, SPDT, 5 amps	SPC21145

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
ASH	02-08-10
CHECKED BY:	DATE:
JAG	14-08-10
APPROVED BY:	DATE:
XXX	16-08-10

DRAWING TITLE: Rocker Switch, SPDT, 5 amps

SIZE	DWG. NO.	ELECTRONIC FILE	REV
XXX	XXX	53H6651	A

SCALE: NTS U.O.M.: INCHES [mm] SHEET: 1 OF 1