



REVISIONS

DOC. NO. SPC-F005 * Effective: 7/5/02 * DCP No: 1398


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2000	A	Released	JN	11/18/08	JWM	11/18/08	JWM	11/18/08



Specifications:

- Terminal: Brass, Tin plated, 0.8 t
- Insulator Body: PBT (UL94V-0), black
- Screw: M3.0, steel, Ni plated
- Cover: PC
- Operating Temperature: -40°C to +120°C
- Rated current: 15Amp AC300V
- Insulation withstands volt: AC2000V min
- Insulation resistance: >5000MW at DC500V
- PCB hole Dia: Ø1.6mm~ Ø1.8mm
- Wire range: 14~22 AWG
- Screw Torque: 12 lb-in

Screw with washer



Unit of Measure: mm

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	11/18/08
CHECKED BY:	DATE:
JWM	11/18/08
APPROVED BY:	DATE:
JWM	11/18/08

DRAWING TITLE:

PCB Tri-Barrler Terminal Block

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	MC24350	14N5679.dwg	A
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	