SPC TECHNOLOGY


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS


DOC. NO. SPC-F005 * Effective: 7/8/02 * ECP No: 1398

ECP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
XX	XX	XXXX	XXXX	29-09-08	XXXX	29-09-08	XXXX	29-09-08
XXXX	XXXX		XXXX	29-09-08	XXXX	29-09-08	XXXX	29-09-08




BUSHING






MODEL NO.	SWITCHING POSITION	
		
SPC21191	ON	MOM
CONN. TERMS	2-1	2-3
SCHEMATIC	SPDT 	



TERMINATION



RoHS Compliant

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
XXXX	29-09-08
CHECKED BY:	DATE:
XXXX	29-09-08
APPROVED BY:	DATE:
XXXX	29-09-08

DRAWING TITLE: PUSHBUTTON SWITCH

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC21191	11M0385	XX

SCALE: NTS | U.O.M.: INCHES [mm] | SHEET: 1 OF 1

SPC TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * ECP No: 1398

ECP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
XX	XX	XXXX	XXXX	29-09-08	XXXX	29-09-08	XXXX	29-09-08
XXXX	XXXX		XXXX	29-09-08	XXXX	29-09-08	XXXX	29-09-08

SPECIFICATIONS

ELECTRICAL

CONTACT RATING:
SILVER: 3A @ 120 VAC OR 28 VDC, 1A @ 250 VAC
GOLD: 0.4 VA MAX. @ 20 V MAX. (AC OR DC)

CONTACT RESISTANCE:	20 MILLIOHMS MAX.
INSULATION RESISTANCE:	1,000 MEGOHMS MIN. AT 500 VDC
DIELECTRIC STRENGTH:	1,000 VRMS

MECHANICAL

LIFE:	60,000 CYCLES

ENVIRONMENTAL

OPERATING TEMPERATURE:	-30°C TO +85°C

MATERIAL

CASE:	DAP, UL 94V-0
HOUSING:	STAINLESS STEEL
ACTUATOR:	THERMOPLASTIC POLYESTER
BUSHING:	BRASS, NICKEL PLATED
SUPPORT:	BRASS, TIN PLATED
CONTACT/TERMINALS:	COPPER ALLOY, SILVER OR GOLD PLATED

REGULATORY

UL AND CANADA RECOGNIZED COMPONENT. UL/CUL FILE NO. E173084.

RoHS Compliant

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
XXXX	29-09-08
CHECKED BY:	DATE:
XXXX	29-09-08
APPROVED BY:	DATE:
XXXX	29-09-08

DRAWING TITLE: PUSHBUTTON SWITCH

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC21191	11M0385	XX

SCALE: NTS | U.O.M.: INCHES [mm] | SHEET: 1 OF