


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/5/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2022	A	RELEASED	JN	1/07/09	JWM	1/07/09	JWM	1/07/09



NOTE:

1. MAXIMUM ELECTRIC CURREENT: $\frac{\text{A.W.G.}}{\text{AMP.}}$

12	10
35	50
6. WIRE RANGE: 12-10 A.W.G (4-6 mm²)
7. TERMINAL SURFACE TREATMENT: TIN PLATED
8. TERMINAL THICKNESS: 1.00mm

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Jason Nash

DATE:

1/07/09

DRAWING TITLE:

Terminal

CHECKED BY:

Jeff McVicker

DATE:

1/07/09

SIZE

A

DWG. NO.

MC29497

ELECTRONIC FILE

34P2255.dwg

REV

A

APPROVED BY:

Jeff McVicker

DATE:

1/07/09

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1