





SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION,
WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED
WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC
TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DCP #	REV	DESCRIPTION	DOC. NO.	SPC-F005	Effective: 7/8/02	DCP No: 1398
			DRAWN	DATE	CHECKD	DATE
			VEE	02-08-10	JAg	03-08-10
						XXX
						16-08-10



Dimensions: millimeter

Specifications:

Electrical:

- Contact rating : 7.5A at 125VAC
- Contact resistance : 5 milliohms maximum
- Insulation resistance : 5000 Megohms minimum at 500VDC
- Dielectric strength : 1400VAC
- Capacitance : 7pF maximum

Mechanical:

- Insertion force : 1.0 to 8.0kg
- Withdrawal force : 1.0 to 8.0kg

Environmental:

- Operating temperature : -55°C to 70°C

Item	Part	Material	Finish
1	Housing	Zinc Die Cast	Nickel
2	Insert Insulator	PTO-1, UL94V-0	Gray
3	Socket	Phosphor Bronze	Silver
4	Cable Relief	PVP	Matte

Part Number Table

Description	Part Number
Female XLR Type Audio Cord Plug	SPC21423

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWING TITLE:

Female XLR Type Audio Cord Plug

DRAWN BY:

VEE

DATE:

02-08-10

CHECKED BY:

JAg

DATE:

03-08-10

APPROVED BY:

XXX

DATE:

16-08-10

SCALE:

NTS

U.O.M.: INCHES [mm]

SHEET:

1

OF 1