


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2013	A	Released	JN	1/05/08	JWM	1/05/08	JWM	1/05/08



**ELECTRICAL**

- CONTACT RATING  
3 CONTACT: 15A @ 125VAC
- CONTACT RESISTANCE: 5 MILLIOHMS MAX.
- INSULATION RESISTANCE: 5000 MEGOHMS MIN.  
@ 500VDC
- DIELECTRIC STRENGTH: 1400VAC
- CAPACITANCE:  
3 CONTACT: 4pF MAX.

**MECHANICAL**

- INSERTION FORCE: 1.0-8.0 Kg
- WITHDRAWAL FORCE: 1.0-8.0 Kg

**ENVIRONMENTAL**

- OPERATING TEMPERATURE: -55°C TO +70°C

Item	Part	Material/Finish
1	Housing	Zinc Die Cast; Black Nickel Finish
2	Insert Insulator	PPT, Gray
3	Socket	Phos. Bronze, Silver Plated

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	Jason Nah	1/05/08	XLR Audio Receptacle, Female			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	Jeff McVicker	1/05/08	A	SPC21492	11M0637.dwg	A
	APPROVED BY:	DATE:	SCALE:	U.O.M.:	SHEET:	
	Jeff McVicker	1/05/08	NTS	MILLIMETERS	1 OF 1	

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.