


DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2070	A	Released	JN	09-03-09	JWM	09-03-09	JWM	09-03-09



Specification

1. Rated Voltage: 6VDC
2. Operating Voltage: 4V ~ 8VDC
3. Max. Rated Current: 15mAat 6VDC
4. Resonant Frequency: 4.8 ± 0.5 KHz
5. Min. Sound Pressure Level: 85dB at 6VDC/30cm
6. Tone Nature: Continuous
7. Case Material: ABS
8. Operating Temperature: $-20 \sim +60^{\circ}\text{C}$
9. Store Temperature: $-30 \sim +70^{\circ}\text{C}$
10. Weigh: 6g

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Jason Nash

DATE:

09-03-09

CHECKED BY:

Jason Nash

DATE:

09-03-09

APPROVED BY:

Jason Nash

DATE:

09-03-09

DRAWING TITLE:

Piezo Buzzer

SIZE

A

DWG. NO.

MCKPI-G2210L-06-3951

ELECTRONIC FILE

25R0625.dwg

REV

A

SCALE:

NTS

U.D.M:

INCHES [mm]

SHEET:

1 OF 1